



Workplace Solutions

UV-resistant markers and hand tools for your Photovoltaic system

The installation and labelling of PV systems are associated with special requirements. It is therefore not only important to use the right materials for labelling, but also professional tools to ensure a perfect connection and long-lasting results.

Special features:

- Weathering resistance tested according to ISO DIN EN ISO 4892-2:2013 Table 3, Method A, Cycle 1 at 5000 hours
- Stripping PV conductors up to 10 mm²
- PV crimping tool for photovoltaic contacts



Printer accessories, markers, cable ties and PV tools

Ordering data

Type		Order No.
PV Markers		
SFX-VT 9/24 MM BL	Cable marker 9x24 mm, with 1 cable tie punchings, UV resistant, blue	2799320000
SFX-VT 9/24 MM GE	Cable marker 9x24 mm, with 1 cable tie punchings, UV resistant, yellow	2621460000
SFX-VT 9/24 MM RT	Cable marker 9x24 mm, with 1 cable tie punchings, UV resistant, red	2799310000
SFX-VT 9/24 MM WS	Cable marker 9x24 mm, with 1 cable tie punchings, UV resistant, white	2621470000
SFX-VT 11/60 MM BL	Cable marker 11x60 mm, with 2 cable tie punchings, UV resistant, blue	2900970000
SFX-VT 11/60 MM GE	Cable marker 11x60 mm, with 2 cable tie punchings, UV resistant, yellow	2621440000
SFX-VT 11/60 MM RT	Cable marker 11x60 mm, with 2 cable tie punchings, UV resistant, red	2900960000
SFX-VT 11/60 MM WS	Cable marker 11x60 mm, with 2 cable tie punchings, UV resistant, white	2621450000
THM PV EL 30 SI 30M	Width 30mm, continuous material, use of cutting blade recommended, silver	2969100000
THM PV EL 30 WS 30M	Width 30mm, continuous material, use of cutting blade recommended, white	2969070000
THM PV EL 60 SI 30M	Width 60mm, continuous material, use of cutting blade recommended, silver	2969090000
THM PV EL 60 WS 30M	Width 60mm, continuous material, use of cutting blade recommended, white	2969060000
THM PV EL 90 GE 30M	Width 90mm, continuous material, use of cutting blade recommended, yellow	2817440000
THM PV EL 90 RT 30M	Width 90mm, continuous material, use of cutting blade recommended, red	2817430000
THM PV EL 90 SI 30M	Width 90mm, continuous material, use of cutting blade recommended, silver	2969080000
THM PV EL 90 WS 30M	Width 90mm, continuous material, use of cutting blade recommended, white	2969050000
THM PV 15/45 TR	Dimension 15x45mm, Can be used as a device marker or protective film for CC or SM, Transparent	2969150000
THM PV 18/9.5 TR	Dimension 18x9.5mm, Can be used as a device marker or protective film for CC or SM, Transparent	2969180000
THM PV 27/12.5 TR	Dimension 12x12.5mm, Can be used as a device marker or protective film for CC or SM, Transparent	2969170000
THM PV 27/18 TR	Dimension 27x18mm, Can be used as a device marker or protective film for CC or SM, Transparent	2969160000
THM PV 30/60 TR	Dimension 30x60mm, Can be used as a device marker or protective film for CC or SM, Transparent	2969130000
THM PV 85/54 TR	Dimension 15x45mm, Can be used as a device marker or protective film for CC or SM, Transparent	2969120000
THM PV 89/60 B/DR RT	Warning red type label, 89x60mm, UV resistant, with preprinted warning flash, red	2817450000
THM PV 90/140 WBC	Information sign for fire brigade according to IEC 62548 Photovoltaic system with battery storage and text field	2986860000
THM PV 90/140 WFF	Information sign for fire brigade according to IEC 62548 Photovoltaic system and text field	2986850000
PV Marker Pocket pack		
TABPACK PV 90/100 WBC	Information sign for fire brigade according to IEC 62548 Photovoltaic system with battery storage	2817470000
TABPACK PV 90/100 WFF	Information sign for fire brigade according to IEC 62548 Photovoltaic system	2817460000
PV Cable ties		
CB-UVR 140/3.5 BK	UV cable ties, 3.5 x 140 mm, polyamide 66, black	2659320000
CB-UVR 200/3.5 BK	UV cable ties, 3.5 x 200 mm, polyamide 66, black	2659330000
CB-UVR 200/4.8 BK	UV cable ties, 4.8 x 200 mm, polyamide 66, black	2659340000
CB-UVR 290/4.5 BK	UV cable ties, 4.5 x 290 mm, polyamide 66, black	2659350000
CB-UVR 365/7.5 BK	UV cable ties, 7.5 x 365 mm, polyamide 66, black	2659360000
PV Printer		
THM MultiMark	Thermal transfer printer for labelling	2599430000
Printing accessories		
RIBBON MM-HS 60/300 SW	Colour tapes for SFX-VT cable markers and shrink sleeves, 60x300.000 mm, black	2448880000
RIBBON MM 84/300 WS	Colour tapes for Labels, 84x300.000 mm, white	2005040000
RIBBON MM 110/300 WS	Colour tapes for Labels, 110x300.000 mm, white	2918800000
RIBBON MM 76/360 SW	Colour tapes for Labels, 76x360.000 mm, black	2005080000
RIBBON MM 110/360 SW	Colour tapes for Labels, 110x360.000 mm, black	2005070000
THM MMP CUTTER	Cutting knife for the THM MultiMark	1331600000

