

Klippon® Relay

TERMSERIES CROSS-CONNECTION

Adaptable cross-connection for the TERMSERIES

Simple and comfortable cross-connection of compact relay modules

Relays modules are used in different industries and applications for isolation and amplifying loads. With the trend towards compact design, slim relays from the TERMSERIES are used, thus making the possibility of cross-connection essential.

The TERMSERIES CROSS-CONNECTION offers more flexibility with regard to the number of poles that can be adapted to the application. The strip material, which can be cut to length as required, with 51 poles considerably reduces the resulting waste.



More
flexibility
through custom
cutting


Your special advantages:




- Additional bar to avoid deformation of the spring
- An additional bar also supports gripping and mounting without having to reach for the contacts
- Individually adjustable cross-connection with 51 poles
- Very simple cutting of the cross-connection to the required length thanks to notches between the poles
- Extended cross-connection possibility up to 32 poles



▶ To the Video
TERMSERIES CROSS-CONNECTION

ERC






discontinued model

Type	Colour	No. of poles	Pitch	Order No.
ZQV 1.5N/R6.4/2 BL	Blue	2	6.4 mm	1446140000
ZQV 1.5N/R6.4/2 GE	Yellow	2	6.4 mm	1193670000
ZQV 1.5N/R6.4/2 RT	Red	2	6.4 mm	1446090000
ZQV 1.5N/R6.4/2 SW	Black	2	6.4 mm	1446040000
ZQV 1.5N/R6.4/10 BL	Blue	10	6.4 mm	1390350000
ZQV 1.5N/R6.4/10 GE	Yellow	10	6.4 mm	1193680000
ZQV 1.5N/R6.4/10 RT	Red	10	6.4 mm	1391640000
ZQV 1.5N/R6.4/10 SW	Black	10	6.4 mm	1391630000
ZQV 1.5N/R6.4/19 BL	Blue	19	6.4 mm	1391620000
ZQV 1.5N/R6.4/19 GE	Yellow	19	6.4 mm	1193690000
ZQV 1.5N/R6.4/19 RT	Red	19	6.4 mm	1391610000
ZQV 1.5N/R6.4/19 SW	Black	19	6.4 mm	1391600000
ZQV 1.5N/R12.8/10 BL	Blue	10	12.8 mm	1445970000
ZQV 1.5N/R12.8/10 GE	Yellow	10	12.8 mm	1193700000
ZQV 1.5N/R12.8/10 RT	Red	10	12.8 mm	1445950000
ZQV 1.5N/R12.8/10 SW	Black	10	12.8 mm	1445940000

new version

Type	Colour	No. of poles	Pitch	Order No.
TCC 6.4/2 BL	Blue	2	6.4 mm	2556430000
TCC 6.4/2 OR	Orange	2	6.4 mm	2556350000
TCC 6.4/2 RD	Red	2	6.4 mm	2556390000
TCC 6.4/2 BK	Black	2	6.4 mm	2556470000
TCC 6.4/10 BL	Blue	10	6.4 mm	2556440000
TCC 6.4/10 OR	Orange	10	6.4 mm	2556360000
TCC 6.4/10 RD	Red	10	6.4 mm	2556400000
TCC 6.4/10 BK	Black	10	6.4 mm	2556480000
TCC 6.4/51 BL	Blue	51	6.4 mm	2556450000
TCC 6.4/51 OR	Orange	51	6.4 mm	2556370000
TCC 6.4/51 RD	Red	51	6.4 mm	2556410000
TCC 6.4/51 BK	Black	51	6.4 mm	2556490000
TCC 12.8/26 BL	Blue	26	12.8 mm	2556460000
TCC 12.8/26 OR	Orange	26	12.8 mm	2556380000
TCC 12.8/26 RD	Red	26	12.8 mm	2556420000
TCC 12.8/26 BK	Black	26	12.8 mm	2556500000



Visit our website for more information
www.weidmueller.com/term



Visit our online catalogue for
more information