

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Connectors

Name and address of the applicant

Weidmüller Interface GmbH & Co. KG
Klingenbergstrasse 26, 32758 Detmold, Germany

Name and address of the manufacturer

Weidmüller Interface GmbH & Co. KG
Klingenbergstrasse 26, 32758 Detmold, Germany

Name and address of the factory

Thüringische Weidmüller GmbH, An der Allee 1
99848 Wutha-Farnroda Germany

When more than one factory

☐ Additional information on page 2

Ratings and principal characteristics

Product data

Rated voltage: 250 V~, 320 V~, 400 V~

Product data – type BLF 5.08HC

Rated current at ambient of 20 °C: 24 A; Rated current at ambient of 40 °C: 21 A

Product data – type BLL 5.08

Rated current at ambient of 20 °C: 23 A; Rated current at ambient of 40 °C: 20 A

Product data – type SL 5.08HC

Rated current at ambient of 20 °C: 24 A; Rated current at ambient of 40 °C: 21 A

Product data – type SLF 5.08

Rated current at ambient of 20 °C: 25,9 A; Rated current at ambient of 40 °C: 22,3 A

Product data – type SLS 5.08

Rated current at ambient of 20 °C: 21,5 A; Rated current at ambient of 40 °C: 18 A

Trademark / Brand (if any)



Weidmüller

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

BLF 5.08HC, BLL 5.08, SLF 5.08, SLS 5.08 and SL 5.08HC

Additional information

☐ Additional information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61984:2008


As shown in the Test Report Ref. No. which forms part of this Certificate

2304485.50

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-03-20


Signature: H.R.M. Barends

