



CERTIFICATE

No. B 033299 0479 Rev. 02

Holder of Certificate: Weidmüller Interface GmbH & Co. KG

Klingenbergstr. 26
32758 Detmold
GERMANY

Certification Mark:



Product: Power supply
(Connect Power)

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 6821020015704

Valid until: 2031-06-23

Date, 2026-06-24

(Yager Bi)



CERTIFICATE

No. B 033299 0479 Rev. 02

Model(s): PRO TOP2 120W 24V 5A UW,
PRO TOP2 120W 24V 5A UW EX

Brand Name: Weidmüller



Parameters:

Rated Input: 100-240VAC, 50/60Hz, 2.0-1.0A; or
Y 230/400-500VAC, 2W+PE, 50/60Hz, 0.7-0.5A; or
320-500VDC, 0.7-0.4A

Rated Output: 24VDC, 5A
Protection Class: I
Degree of Protection: IP20

Remarks:

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Clearance was evaluated for operating altitude up to 5000m above sea level.
- Built-in type equipment, suitable enclosure and type of supply connection should be provided by end system.
- When installing the equipment into end system, care must be taken that the output and associated wire(s) may not be touched.
- These power supplies can only be used in equipment which provides with reliable earthing.
- Refer to installation instructions for details of loading condition and input voltage and operating ambient temperature.
- The DC input of these power supplies shall be driven from the end system of maximum 300VAC mains supply.

Tested according to: EN IEC 62368-1:2024/A11:2024