



CERTIFICATE

No. B 033299 0549 Rev. 01

Holder of Certificate: Weidmüller Interface GmbH & Co. KG
Klingenbergstr. 26
32758 Detmold
GERMANY

Certification Mark:



Product: Power supply
(Switching Power Supply)

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 6821021025402

Valid until: 2031-06-24

Date, 2026-06-25

(Yager Bi)



CERTIFICATE

No. B 033299 0549 Rev. 01

Model(s): PRO TOPDC 24V/24V 5A, PRO TOPDC 24V/24V 5A EX

Brand Name: Weidmüller



Parameters:

Rated Input: 24VDC, 5.7A
Rated Output: 24VDC, 5A
Degree of Protection: IP20

Remarks:

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Built-in component, suitable enclosure should be provided by end system.
- Clearance was evaluated for operating altitude up to 5000m above sea level.
- The maximum operating temperature is 70°C. Refer to the installation and operating instruction from manufacturer for the details of loading condition and operating ambient temperature.
- Basic insulation is provided between input circuit and output circuit, and between input circuit and metal enclosure/protective bonding conductor.
- This built-in equipment should be connected to a source which is insulated from the mains supply by double or reinforced insulation.

Tested according to: EN IEC 62368-1:2024/A11:2024