



CERTIFICATE

No. B 033299 0485 Rev. 02

Holder of Certificate: **Weidmüller Interface GmbH & Co. KG**

Klingenbergstr. 26
32758 Detmold
GERMANY

Certification Mark:



Product: **Power supply
(Connect Power)**

The product was tested on a voluntary basis and complies with the essential requirements.
The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier.
All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 6821020008204

Valid until: 2031-06-22

Date, 2026-06-23

(Yager Bi)



CERTIFICATE

No. B 033299 0485 Rev. 02

Model(s): PRO TOP2 240W 48V 5A UW, PRO TOP2 240W 24V 10A UW,
PRO TOP2 240W 24V 10A UW EX

Brand Name: Weidmüller



Parameters:

Rated Input:
100-240VAC, 50/60Hz, 3-1.3A; or
Y 230/400-500VAC, 2W+PE, 50/60Hz, 1.4-0.8A; or
320-500VDC, 0.9-0.6A
Rated Output:
48VDC, 5A (for PRO TOP2 240W 48V 5A UW)
24VDC, 10A (for PRO TOP2 240W 24V 10A UW and PRO TOP2 240W 24V 10A UW EX)
Protection Class: I
Degree of Protection: IP20

Remarks:

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Built-in type equipment, suitable enclosure and type of supply connection should be provided by end system.
- Refer to installation instructions for details of loading condition and input voltage and operating ambient temperature.
- Clearance was evaluated for operating altitude up to 5000m above sea level.
- These products only can be used in pluggable equipment type B, permanently connected equipment, or pluggable equipment type A which provided with permanently connected earthing terminal.

Tested according to: EN IEC 62368-1:2024/A11:2024