



CERTIFICATE

No. B 033299 0387 Rev. 04

Holder of Certificate: **Weidmüller Interface GmbH & Co. KG**

Klingenbergstr. 26
32758 Detmold
GERMANY

Certification Mark:



Product: **Switching power supply unit
(Connect Power)**

The product was tested on a voluntary basis and complies with the essential requirements.
The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier.
All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 6821017057506

Valid until: 2031-06-23

Date, 2026-06-24

(Yager Bi)



CERTIFICATE

No. B 033299 0387 Rev. 04

Model(s): PRO TOP1 120W 24V 5A,
PRO TOP1 120W 24V 5A F,
PRO TOP1 120W 24V 5A EX,
PRO TOP1 120W 12V 10A,
PRO TOP1 120W 12V 10A F,
PRO TOP1 120W 12V 10A EX

Brand Name: Weidmüller



Parameters:

Ratings:

Input:

100-240VAC, 50/60Hz, 2.0-1.0A or 120-340VDC, 2.0-0.6A

Output:

24VDC, 5A (For models: PRO TOP1 120W 24V 5A, PRO TOP1 120W 24V 5A F, PRO TOP1 120W 24V 5A EX);

12VDC, 10A (For models: PRO TOP1 120W 12V 10A, PRO TOP1 120W 12V 10A F, PRO TOP1 120W 12V 10A EX)

Protection Class: I

Degree of Protection: IPX0

Remarks:

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Built-in type component, suitable enclosure should be provided by end system.
- Clearance was evaluated for operating altitude up to 5000m above sea level.
- Refer to the installation and operating instruction from manufacturer for the details of loading condition and operating temperature.

Tested according to: EN IEC 62368-1:2024/A11:2024