



CERTIFICATE

No. B 033299 0419 Rev. 04

Holder of Certificate: Weidmüller Interface GmbH & Co. KG

Klingenbergstr. 26
32758 Detmold
GERMANY

Certification Mark:



Product: Switching power supply unit
(Switching Power Supply)

The product was tested on a voluntary basis and complies with the essential requirements.
The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier.
All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 6821018043306

Valid until: 2031-06-23

Date, 2026-06-24

(Yager Bi)



CERTIFICATE

No. B 033299 0419 Rev. 04

Model(s): PRO TOP3 240W 24V 10A,
PRO TOP3 240W 24V 10A CO

Brand Name: Weidmüller



Parameters:

Rated Input: 3x400-500VAC, 50/60Hz, 3x0.6-0.5A or
450-500VDC, 0.7-0.6A

Rated Output: 24VDC, 10A

Protection Class: I

Degree of Protection: IPX0

Remarks:

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- The maximum operating temperature is 70°C.
- Clearance was evaluated for operating altitude up to 5000m above sea level.
- Built-in type equipment, suitable enclosure and type of supply connection should be provided by end system.
- External 2-3A, min. 500VAC/DC non-time delayed fuse or breaker should be provided before each input (L1, L2, L3) of this power supply for protection when installed into the end system.
- When installing the equipment into end system, care must be taken that the output and associated wire(s) may not be touched.
- Reinforced or double insulation is provided between input circuit and output circuit, and basic insulation is provided between input circuit and metal enclosure/PE.

Tested according to: EN IEC 62368-1:2024/A11:2024