

Document No. **UKCA DE PA5200 211116 002 ISS 01**

Manufacturer **Weidmüller Interface GmbH & Co. KG**

Address **Klingenbergstr. 26  
32758 Detmold, Germany**

Object of the declaration **PROmax Series**

☒ Continued on page 2

The manufacturer attests, in sole-responsibility, that the object of the declaration described above is in conformity with the essential requirements of directive(s):

|                                                                                                                                                                                      |                     | Directive                                      |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|------------------------------------------------|
| <input checked="" type="checkbox"/> The Electrical Equipment (Safety) Regulations 2016                                                                                               | <b>SI 2016/1101</b> | <b>SI2019/696(Schedule23)<br/>SI 2020/1460</b> |
| <input checked="" type="checkbox"/> The Electromagnetic Compatibility Regulations 2016                                                                                               | <b>SI 2016/1091</b> | <b>SI2019/696(Schedule20)<br/>SI 2020/1460</b> |
| <input type="checkbox"/> The supply of Machinery (Safety) Regulations 2008                                                                                                           | <b>SI 2008/1597</b> | <b>SI2019/696(Schedule12)<br/>SI 2020/1460</b> |
| <input type="checkbox"/> The Radio Equipment Regulations 2017                                                                                                                        | <b>SI 2017/1206</b> | <b>SI2019/696(Schedule29)<br/>SI 2020/1460</b> |
| <input checked="" type="checkbox"/> The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 RoHS                          | <b>SI 2012/3032</b> | <b>SI2019/188</b>                              |
| <input type="checkbox"/> The Equipment and Protective Systems Intended for Use in Potentially Explosive Atmospheres Regulations 2016 Marking (Equipment Group, Category, Atmosphere) | <b>SI 2016/1107</b> | <b>SI2019/696Schedule25)<br/>SI 2020/1460</b>  |

References to the relevant EN or BSEN designated standards used, or references to the specifications, in relation to which conformity is declared:



Document No. **UKCA DE PA5200 211116 002 ISS 01**

Issued certificates from notified bodies:

NSR / LVD  
EN 62368-1:2014+A11:2017EMV / EMC:  
EN 55032:2015  
EN 55024:2010+A1:2015  
EN 55035:2017  
EN 61000-3-2:2014  
EN 61000-3-3:2013RoHS:  
EN IEC 63000:2018

Object of the declaration (continued from page 1)

| Art.Bez.              | Best.-Nr.  |
|-----------------------|------------|
| Typ                   | Order No.  |
| PRO MAX 120W 12V 10A  | 1478230000 |
| PRO MAX 120W 24V 5A   | 1478110000 |
| PRO MAX 180W 24V 7,5A | 1478120000 |
| PRO MAX 240W 24V 10A  | 1478130000 |
| PRO MAX 240W 48V 5A   | 1478240000 |
| PRO MAX 480W 24V 20A  | 1478140000 |
| PRO MAX 480W 48V 10A  | 1478250000 |
| PRO MAX 70W 5V 14A    | 1478210000 |
| PRO MAX 72W 12V 6A    | 1478220000 |
| PRO MAX 72W 24V 3A    | 1478100000 |
| PRO MAX 960W 24V 40A  | 1478150000 |
| PRO MAX 960W 48V 20A  | 1478270000 |
| PRO MAX3 120W 24V 5A  | 1478170000 |
| PRO MAX3 240W 24V 10A | 1478180000 |
| PRO MAX3 480W 24V 20A | 1478190000 |
| PRO MAX3 960W 24V 40A | 1478200000 |

Detmold, 16.11.2021  
place, date

name and function

  
legally binding signature

Sascha Dreifert

Leiter BU Power Supplies & Interface Electronics /  
Vice President BU Power Supplies & Interface Electronics

This declaration certifies compliance with the indicated directive but no warranty of properties. The safety instructions of the accompanying product documentation shall be observe.