



BVZ 7.62IT/04/180M(S)F4



For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.





Weidmüller PCB components are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

HINWEIS: QR Code bitte noch nicht berücksichtigen!  
 INFORMATION: Please do not consider the QR code yet

P = RASTER/PITCH  
 MF = MITTEFLANSCH/MIDDLE FLANGE  
 PE = POTENTIAL ERDE/GROUND  
 n = POLZAHL/NO. OF POLES  
 POL = POL/POLES

BVZ7.62IT/03/180 MF 2	POL	MF	POL	POL	
BVZ7.62IT/04/180 MF 3	POL	POL	MF	POL	POL
BVZ7.62IT/04/180 MF 4	POL	POL	POL	MF	POL
BVZ7.62IT/04/180 MF 2	POL	MF	POL	POL	POL
BEZEICHNUNG/ PART NAME	1	2	3	4	5
POSITION					
n					L1

 EC00001333 First Issue Date 24.06.2011	Prim PLM Part No.: 011202		Prim ERP Part No.: 1312730000
	Max. nos.		Modification
	Date	Name	
	Drawn	29.04.2019	Helis, Maria
	Responsible		Döhrer, Karl
Scale: 2:1	Size: A3	Approved	14.05.2019
		Lang, Thomas	
Drawings Assembly			
Product file: 7391 BVZ7.62HP_MF			

BVZ 7.62IT/04/180M(S)F2  
1:1BVZ 7.62IT/04/180M(S)F4  
1:1BVZ 7.62IT/04/180M(S)F3  
1:1BVZ 7.62IT/04/180M(S)F1  
1:1

7	53,34	2,10
6	45,72	1,80
5	38,10	1,50
4	30,48	1,20
3	22,86	0,90
2	15,24	0,60
	MM	INCH
n		L1

**50052**  
 Drawing no. 16  
 Issue no.

Sheet 02 of 05 sheets

**BVZ 7.62IT/..180MF...**  
 BUCHSENLEISTE  
 SOCKET BLOCK