

8000060710 PV combiner box thermal report**PV 232S0F4CXXV0O3TXPX15PWW****INPUT DATA**


Enclosure model	847 x 636 x 300 mm
Number of MPPT	1
Switch-disconnector model (per MPPT)	400A 1500V
Maximum current (per MPPT)	320 A
Number of inputs (per MPPT)	32
Fuse-link model	20A gPV 1500V 10x85mm
Number of Transclinic xi+ devices (per MPPT)	0
Type of mounting	Against wall, all other sides detached
Maximum allowed internal temperature	70 °C
Combined inputs	1
Height (A)	847 mm
Width (B)	636 mm
Depth (C)	300 mm
Effective cooling surface A_e of the enclosure	1.48 m ²

RESULTS

Ambient temperature (no direct sunlight)	50 °C
Rated current per input at 50°C	10.00 A
Power dissipated by components (except wiring)	74 W
Power dissipated by wiring	19 W
Total dissipated power	93 W
Temperature rise, mid height	16 °C
Temperature rise, top	20 °C
Internal temperature, top	70 °C

CURRENT RATINGS

At 35°C	10.00 A
At 40°C	10.00 A
At 45°C	10.00 A
At 50°C	10.00 A

**NOTES**

Thermal report based on IEC TR 60890 ed2.0

Thermal report does not include the direct sunlight effects