

**Report No.: TR1907260402**

**Product: DIN-Rail Power Supply**

**Model: PRO TOP1 120W 24V 5A EX,**

**PRO TOP1 120W 12V 10A EX**

**Prepared For: Weidmueller Interface GmbH & Co.KG**

**Klingenbergsstraße 26,  
D-32758 Detmold, Germany**

**Prepared By: Delta Technology Service (Shenzhen) Co., Ltd.**

**1-01, Building 1& 1-01 A-01, Building 3, No.15  
Jinhui Rd., Kengzi Subdistrict, Pingshan  
District, Shenzhen, 518122, P.R.China**

**Operator:  
(+ signature)**

Wen Wei, Engineer

检测报告章

2019.9.29

**Reviewer:  
(+ signature)**

Wang Shiyu, Sr.Staff Engineer

2019.9.29

### Comments

1. The laboratory has obtained the accreditation of China National Accreditation Committee for Laboratories (CNAL), and accreditation number: CNAS L10153.
2. The laboratory has obtained the accreditation of DNV-GL, and accreditation number: 639-18-LAB 39.
3. The test report is invalid if not marked with "exclusive stamp for the test report".
4. Any copy of the test report is invalid if not re-marked with the "exclusive stamp for the test report".
5. The test report is invalid if not marked with the stamps or the signatures of the persons responsible for performing, revising and approving the test report.
6. The test report is invalid if there is any evidence of erasure and/or falsification.
7. If there is any dissidence for the test report, please file objection to the test lab within 30 days from the date of receiving the test report.
8. Normally, the test report is only responsible for the samples that have undergone the test.
9. Context of the test report cannot be used partially or in full for publicity and/or promotional purposes without previous written approval of the laboratory.

Manufacturer's name and address .. : **Weidmueller Interface GmbH & Co.KG**

**Klingenbergsstraße 26,  
D-32758 Detmold, Germany**

Factory's name and address ..... : **Weidmueller Interface GmbH & Co.KG**

**Klingenbergsstraße 26,  
D-32758 Detmold, Germany**

Product..... :  
DIN-Rail Power Supply  
PRO TOP1 120W 24V 5A EX,  
PRO TOP1 120W 12V 10A EX

Standard ..... : ISA 71.04 G3 and the client's requirement

Non-standard test method..... : --

Test purpose ..... : Validate the samples are whether meet the requirements of ISA 71.04 G3 and the client's requirement

Test result..... : Test results show that equipment under test to meet the requirements of ISA 71.04 G3 and the client's requirement