

# CERTIFICATE

DEKRA

Issued to:

Applicant:  
**Weidmüller Interface GmbH & Co. KG**  
**Klingenbergsstrasse 16**  
**32758 Detmold, Germany**

Licensee:  
**Weidmüller Interface GmbH & Co. KG**  
**Klingenbergsstrasse 16**  
**32758 Detmold, Germany**

Product : Terminal Blocks for copper conductors  
Trade name(s) : Weidmüller  
Type(s)/model(s) : BK 12/E, BK 2/E, BK 3/E, BK 4/E and BK 6/E

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 60947-7-1:2009
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 900119


DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration of the KEMA-KEUR certification agreement and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 12 December 2018 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-106152

DEKRA Certification B.V.



B.T.M. Holtus  
Managing Director



RZH Zhou  
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE  
DUTCH ACCREDITATION  
COUNCIL



**SPECIFICATION OF THE CERTIFIED PRODUCT****Product data**

Product	: Terminal Blocks for copper conductors
Trade name(s)	: Weidmüller
Type(s)/model(s)	: BK 12/E, BK 2/E, BK 3/E, BK 4/E and BK 6/E
Rated Voltage	: 400 V
Rated Current	: 32 A
Impulse withstand voltage	: 6 kV
Rated cross section	: 4 mm <sup>2</sup>
Pollution degree	: 3
Stripping length	: 8 mm
Tightening torque	: 0,5 Nm
Connecting capacity	: 0,5 - 4 mm <sup>2</sup> solid and flexible

**Product data – type BK 12/E**

Number of poles	: 12
Number of terminals	: 24

**Product data – type BK 2/E**

Number of poles	: 2
Number of terminals	: 4

**Product data – type BK 3/E**

Number of poles	: 3
Number of terminals	: 6

**Product data – type BK 4/E**

Number of poles	: 4
Number of terminals	: 8

**Product data – type BK 6/E**

Number of poles	: 6
Number of terminals	: 12

**TESTS****Test requirements**

EN 60947-7-1:2009

**Test result**

The test results are laid down in DEKRA test file 222855300.

**Conclusion**

The examination proved that all requirements were met.

**Factory location**

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstrasse 16  
32758 Detmold, Germany