






PCB LAYOUT



STIFTLÄNGE L PIN LENGTH L	TOLERANZ TOLERANCE
3.5	0.2
	-0.2

KUNDENZEICHNUNG CUSTOMER DRAWING

16	52.50	2.068
15	49.00	1.930
14	45.50	1.792
13	42.00	1.654
12	38.50	1.516
11	35.00	1.378
10	31.50	1.240
9	28.00	1.102
8	24.50	0.965
7	21.00	0.827
6	17.50	0.689
5	14.00	0.551
4	10.50	0.413
3	7.00	0.276
2	3.50	0.138
N	L1 [mm]	L1 [inch]

Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application. Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

GENERAL TOLERANCE: DIN ISO 2768-m						CAT.NO.: .		
	85497/5 08.01.16 MA_J	01			C 41693 06		DRAWING NO. ISSUE NO. SHEET 01 OF 01 SHEETS	
	MODIFICATION							
		DATE	NAME	PS 3.5/.../90 ... LEITERPLATTENKLEMME PCB TERMINAL				
	DRAWN	12.04.2005	HE_J					
	RESPONSIBLE		MA_J					
SCALE: 3/1	CHECKED	08.01.2016	ZHOU_N					
SUPERSEDES: .	APPROVED		XU_S	PRODUCT FILE: PS 3.5				7061