


PLC System Cabling

Interfaces and Pre-assembled cables for Siemens S7-1200



Universal solutions for PLC input/output cards

Aimed at reducing costs, and to save space and time in the construction of electrical cabinets, the universal cabling system for PLCs is provided as an effective alternative to end-to-end cabling design. Weidmüller offers a wide range of pre-assembled cables and interfaces:

- The interfaces are used as an interconnection element between the control and the process, and are supplied with tension clamp or screw connection. Those interfaces, with a compact design, provide different functions such as LEDs, fuses, disconnectors or relays.
- The pre-assembled cables are supplied with the manufacturer's own connector at one end and are available in different lengths.

Product Finder and automatic selection guides:

To help you choose the right products for your application, Weidmüller offers this **Product finder** with a selection table which can be found on the following pages.

In addition, on our website, we have an automatic selection guide, using intuitive software that can help you to choose the appropriate interface cable for your Input/Output cards. This can be found at www.weidmueller.com

The screenshot shows the Weidmüller website's 'Product assistant' interface. At the top, there are navigation links for 'Product catalogue', 'Website', and 'English'. The main header features the Weidmüller logo and a shopping cart icon with '0' items. Below the header, the breadcrumb trail reads: 'Product Catalogue >> Product assistant >> Interface units and preconfigured cables for PLC and Weidmüller u-remote'. There are links for 'Restart' and 'Parts list'. The main heading is 'Selection wizard for pre-assembled cables for PLC interface units and Weidmüller u-remote'. A sub-heading explains: 'The selection wizard allows you to quickly find interface units and the matching pre-assembled cables for your existing PLC systems or Weidmüller u-remote.' The first step is '1. Selection of PLC or Weidmüller u-remote', which is currently expanded. It contains two sections: 'Search for PLC' with a text input field for 'PLC or Weidmüller u-remote name' and a 'Search' button; and 'Selection of PLC according to manufacturer or Weidmüller u-remote specifications' with a dropdown menu for 'Manufacturer', a text input for 'Channels per card or Weidmüller u-remote', and a text input for 'Card or module name'. Below this, steps '2. Interface unit selection' and '3. Cable selection' are listed with plus signs. A QR code is located in the bottom right corner of the screenshot area.

Access to Weidmüller Product Finder:
http://galaxy.weidmueller.com/wi_plc

Interfaces and Pre-assembled cables for Siemens S7-1200

The following selection tables help you to choose the pre-assembled cables

1. Select the PLC card from the corresponding table

For example: 6ES7221-1BH30-0XB0

2. Check the code of the cable to be ordered:

- Cable code 1329120xxx
- Quantity: 1 unit (by card)

The last 3 digits indicate the length:
For example, 015 indicates 1.5 m

3. Locate the module family and the quantity required

Example: H2016 System Quantity: 1 unit (by card) or I2016 System Quantity: 1 unit (by card)
Take the notes into account (if there are any)

4. Once the module family is chosen (step 3 - eg H2016), search it in the Interface selection tables and choose the proper interface according to the need of the application: 1, 2 or 3 wires, screw or tension clamp connection, with fuse, LED, switch.

In the case that an input/output card does not appear in this table, you can check our on-line PLC selection guide at www.weidmueller.com where you will always find the most up-to-date information.

| | PLC | | Cables | | Interfaces | | | | | |
|--------------------|--------------------|-------------------------|------------|----------|-----------------------|----------|------------------|----------|-------------------|----------|
| | Input/Output cards | | Standard | | Direct inputs/outputs | | Insulated inputs | | Insulated outputs | |
| | Manufacturer code | Number/Type of channels | Order No. | Quantity | Type | Quantity | Type | Quantity | Type | Quantity |
| DI | 6ES7221-1BF30-0XB0 | 8 DI | 1329110xxx | 1 | H2008 | 1 | | | | |
| | 6ES7221-1BF32-0XB0 | 8 DI | 1329110xxx | 1 | H2008 | 1 | | | | |
| | 6ES7221-1BH30-0XB0 | 16 DI | 1329120xxx | 1 | H2016 | 1 | I2016 | 1 | | |
| | 6ES7221-1BH32-0XB0 | 16 DI | 1329120xxx | 1 | H2016 | 1 | I2016 | 1 | | |
| DO | 6ES7222-1HH30-0XB0 | 16 DO | 1329140xxx | 1 | R2416 | 1 | | | | |
| | 6ES7222-1BF30-0XB0 | 8 DO | 1329150xxx | 1 | H2008 | 1 | | | O2008 | 1 |
| | 6ES7222-1BH30-0XB0 | 16 DO | 1329170xxx | 1 | H2016 | 1 | | | O2016 | 1 |
| | 6ES7222-1BH32-0XB0 | 16 DO | 1329170xxx | 1 | H2016 | 1 | | | O2016 | 1 |
| DI/DO | 6ES7223-1PL30-0XB0 | 16 DI | 1329200xxx | 1 | H2016 | 1 | | | | |
| | | 16 DO | 1329210xxx | 1 | R2416 | 1 | | | | |
| | 6ES7223-1BH30-0XB0 | 8 DI | 1329180xxx | 1 | H2008 | 1 | | | | |
| | | 8 DO | 1329230xxx | 1 | H2008 | 1 | | | O2008 | 1 |
| | 6ES7223-1BL30-0XB0 | 16 DI | 1329200xxx | 1 | H2016 | 1 | | | | |
| | | 16 DO | 1329240xxx | 1 | H2016 | 1 | | | O2016 | 1 |
| 6ES7223-1BL32-0XB0 | 16 DI | 1329200xxx | 1 | H2016 | 1 | | | | | |
| 6ES7223-1BL32-0XB0 | 16 DO | 1329240xxx | 1 | H2016 | 1 | | | O2016 | 1 | |
| AI | 6ES7231-4HD30-0XB0 | 4 AI | 1329250xxx | 1 | A1504 | 1 | | | | |
| | 6ES7231-4HD32-0XB0 | 4 AI | 1329250xxx | 1 | A1504 | 1 | | | | |
| | 6ES7231-4HF30-0XB0 | 8 AI | 1329270xxx | 1 | A2508 | 1 | | | | |
| AO | 6ES7232-4HB30-0XB0 | 2 AO | 1329280xxx | 1 | A1504 | 1 | | | | |
| | 6ES7232-4HD30-0XB0 | 4 AO | 1329290xxx | 1 | A1504 | 1 | | | | |
| AI/AO | 6ES7234-4HE30-0XB0 | 4 AI + 2 AO | 1329300xxx | 1 | A2508 | 1 | | | | |

Note

- Please, always take into account the characteristics of the PLC card (voltage, current...) when selecting interfaces.
In some cases, the card can work at higher voltages than those indicated in the interface.
 - Cables 7789100xxx, 7789104xxx, 7789106xxx, 7789108xxx, 1350480xxx, 1350490xxx and 1350500xxx have wire-end ferrules at one end. These cables do not have a PLC connector. Colour code according to DIN 47100.
 - The interfaces are intended to be used inside an IP20 enclosure at least.
 - The last 3 digits of the cable code indicate its length in decimetres. For example, if the code ends in 100, the cable would be 10 m long.
- * In the case that an input/output card does not appear in this table, you can check our on-line PLC selection guide at www.weidmueller.com where you will always find the most up-to-date information.

Selection table for digital input/output cards with direct wiring interfaces

H20

1:1

- 20-pole ribbon connector
- Connection 1 to 1



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 0224261001 | 8537110000 |

H2008

2 wires

- 8 channels
- 20-pole ribbon connector
- Direct wiring



| | Screw | T. clamp |
|----------|------------|-----------|
| with LED | 9445530000 | on demand |

R1208

2 wires

- 8 channels
- 12-poles RSV connector
- Direct wiring




| | Screw | T. clamp |
|-------------|------------|-----------|
| without LED | 9441540000 | on demand |

H40

1:1

- 40-pole ribbon connector
- Connection 1 to 1



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 0224461001 | 8537140000 |

H2016

1 wire

- 16-channel
- 20-pole ribbon connector
- Direct wiring



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 9445700000 | 1311750000 |
| with LED | 9445710000 | 1311770000 |

1 wire

- 16-channel
- 20-pole ribbon connector
- Disconnector



| | Screw | T. clamp |
|----------|------------|------------|
| with LED | 9445810000 | 1311780000 |

2 wires

- 16-channel
- 20-pole ribbon connector
- Direct wiring



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 9445720000 | 1311790000 |
| with LED | 9445730000 | 1311800000 |

2 wires

- 16-channel
- 20-pole ribbon connector
- Disconnector



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 1311810000 | 1311820000 |
| with LED | 9445750000 | 1311830000 |

2 wires

- 16-channel
- 20-pole ribbon connector
- Fus



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 9445820000 | 1311840000 |
| with LED | 1311850000 | 1311870000 |

3 wires

- 16-channel
- 20-pole ribbon connector
- Direct wiring



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 9445760000 | 1311880000 |
| with LED | 9445770000 | 1311890000 |

R2416

1 wire

- 16-channel
- 24-pole RSV connector
- Direct wiring



| | Screw | T. clamp |
|-------------|------------|-----------|
| without LED | 9441500000 | On demand |

1 wire

- 16-channel
- 24-pole RSV connector
- Disconnector



| | Screw | T. clamp |
|-------------|------------|-----------|
| without LED | 9441860000 | On demand |

2 wires

- 16-channel
- 24-pole RSV connector
- Direct wiring



| | Screw | T. clamp |
|-------------|------------|-----------|
| without LED | 9441700000 | On demand |

2 wires

- 16-channel
- 24-pole RSV connector
- Fus



| | Screw | T. clamp |
|-------------|------------|-----------|
| without LED | 9441560000 | On demand |

3 wires

- 16-channel
- 24-pole RSV connector
- Disconnector



| | Screw | T. clamp |
|-------------|------------|-----------|
| without LED | 9441600000 | On demand |

R3632

1 wire

- 32-channel
- 36-pole RSV connector
- Direct wiring



| | Screw | T. clamp |
|-------------|------------|-----------|
| without LED | 9441510000 | On demand |

1 wire

- 32-channel
- 36-pole RSV connector
- Disconnector



| | Screw | T. clamp |
|-------------|------------|-----------|
| without LED | 9441870000 | On demand |

2 wire

- 32-channel
- 36-pole RSV connector
- Direct wiring



| | Screw | T. clamp |
|-------------|------------|-----------|
| without LED | 9441710000 | On demand |

2 wires

- 32-channel
- 36-pole RSV connector
- Fus



| | Screw | T. clamp |
|-------------|------------|-----------|
| without LED | 9441570000 | On demand |

Selection table for analogue input/output cards with direct wiring interfaces

A15

1:1

- 15-pole male, Sub-D connector
- Connection 1 to 1



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 8005201001 | 8537390000 |

A1504

- 4 channels
- 15-pole male, Sub-D connector
- Direct wiring



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 9448000000 | 1308230000 |

- 4 channels
- 15-pole male, Sub-D connector
- Test point and disconnecter



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 9448100000 | 1308240000 |

A25

1:1

- 25-pole male, Sub-D connector
- Connection 1 to 1



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 8005181001 | 8537370000 |


A2508

- 8 channels
- 25-pole male, Sub-D connector
- Direct wiring



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 9448010000 | 1308250000 |

- 8 channels
- 25-pole male, Sub-D connector
- Test point and disconnecter



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 9448110000 | 9449110000 |

A37

1:1

- 37-pole male, Sub-D connector
- Connection 1 to 1



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 8003881001 | 8537240000 |

A3716

- 16 channels
- 37-pole male, Sub-D connector
- Direct wiring



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 9448020000 | 1308270000 |

- 16 channels
- 37-pole male, Sub-D connector
- Test point and disconnecter



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 9448120000 | 1308280000 |

A50

1:1

- 50-pole male, Sub-D connector
- Connection 1 to 1



| | Screw | T. clamp |
|-------------|------------|------------|
| without LED | 8005161001 | 8537350000 |


A2508P

- 8 channels
- 25-pole male, Sub-D connector
- Voltage/current configuration





| | Screw | T. clamp |
|-------------|------------|-----------|
| without LED | 9448030000 | On demand |


Selection table for digital input cards with isolated interfaces


| I2016 | | |
|--|--------------|-----------------|
| Slim relay 1CO 6A | | |
| <ul style="list-style-type: none"> • 16-channel • 20-pole ribbon connector • Gold contact relay  | | |
| | Screw | T. clamp |
| 24 V DC Input | 1312000000 | 1312010000 |
| 48 V DC Input | 1312020000 | |


Selection table for digital output cards with isolated interfaces


| O2008 | | |
|---|--------------|-----------------|
| Slim relay 1CO 6A | | |
| <ul style="list-style-type: none"> • 8-channel • 20-pole ribbon connector • 1 Changeover  | | |
| | Screw | T. clamp |
| without SWITCH | 1456540000 | 1456570000 |
| with SWITCH | 1128990000 | 1129000000 |


| Relay 1CO 16A | | |
|---|--------------|-----------------|
| <ul style="list-style-type: none"> • 8-channel • 20-pole ribbon connector • 1 Changeover  | | |
| | Screw | T. clamp |
| without SWITCH | 9445000000 | 9447000000 |


| O2016 (positive switching) | | | |
|--|--------------|-----------------|--|
| Slim relay 1CO 6A | | | |
| <ul style="list-style-type: none"> • 16-channel • 20-pole ribbon connector • 1 Changeover  | | | |
| | Screw | T. clamp | |
| without SWITCH | 1457300000 | 1457320000 | |
| with SWITCH | 1129030000 | 1129040000 | |


| Relay 1CO 16A | | |
|--|--------------|-----------------|
| <ul style="list-style-type: none"> • 16-channel • 20-pole ribbon connector • 1 Changeover  | | |
| | Screw | T. clamp |
| without SWITCH | 1448280000 | 1448300000 |
| with SWITCH | 1129120000 | 1129130000 |


| Relay 1CO 16A | | |
|---|--------------|-----------------|
| <ul style="list-style-type: none"> • 16-channel • 20-pole ribbon connector • 1 Changeover  | | |
| | Screw | T. clamp |
| without SWITCH | 9445100000 | 9447100000 |


| Relay 1CO 16A + Fus | | |
|---|--------------|-----------------|
| <ul style="list-style-type: none"> • 16-channel • 20-pole ribbon connector • 1 changeover with fus  | | |
| | Screw | T. clamp |
| without SWITCH | 9445120000 | 9447120000 |

| Relay 1CO 16A + Disconnectors | | |
|---|--------------|-----------------|
| <ul style="list-style-type: none"> • 16-channel • 2x 20-pole ribbon connector • 1 changeover with disconnector  | | |
| | Screw | T. clamp |
| without SWITCH | 1431720000 | On demand |


| Relay 2CO 8A | | |
|--|--------------|-----------------|
| <ul style="list-style-type: none"> • 16-channel • 20-pole ribbon connector • 2 Changeover  | | |
| | Screw | T. clamp |
| without SWITCH | 1449210000 | 1449230000 |

| O2016N (Negative switching) | | |
|--|--------------|-----------------|
| Slim relay 1CO 6A | | |
| <ul style="list-style-type: none"> • 16-channel • 20-pole ribbon connector • 1 Changeover  | | |
| | Screw | T. clamp |
| without SWITCH | 1457310000 | 1457330000 |

| Relay 1CO 16A | | |
|--|--------------|-----------------|
| <ul style="list-style-type: none"> • 16-channel • 20-pole ribbon connector • 1 Changeover  | | |
| | Screw | T. clamp |
| without SWITCH | 1448290000 | 1448310000 |

| Relay 2CO 8A | | |
|---|--------------|-----------------|
| <ul style="list-style-type: none"> • 16-channel • 20-pole ribbon connector • 2 Changeover  | | |
| | Screw | T. clamp |
| without SWITCH | 1449220000 | 1449250000 |


Main advantages



Wide range of passive interfaces

The range includes passive input/output interfaces for digital and analogue signals. The interfaces are available in screw or tension clamp connection and the sensors/actuators can be connected with 1, 2 or 3 wires, whichever is needed. You can also choose from a large variety of functions:

- LED indication
- Fuse
- Disconnectors
- Test points



Wide range of relay insulated interfaces

Available in versions with 8-12 and 16 relays, the RSM family offers the possibility of insulating digital signals both in input and output cards.

Options include our compact format (6 mm relays) or standard (RCL relay), with additional features including:

- Switch in coil and contact
- Fuse in contact
- 1 or 2 CO contacts



Guaranteed connection

The original PLC connector is on one end of the cable and standard connectors are on the other end: ribbon cable with fixing housing for digital signals and SUB-D connector for analogue signals. Available in different lengths.

Weidmüller – Your partner in Smart Industrial Connectivity

As experienced experts we support our customers and partners around the world with products, solutions and services in the industrial environment of power, signal and data. We are at home in their industries and markets and know the technological challenges of tomorrow. We are therefore continuously developing innovative, sustainable and useful solutions for their individual needs. Together we set standards in Smart Industrial Connectivity.

We cannot guarantee that there are no mistakes in the publications or software provided by us to the customer for the purpose of making orders. We try our best to quickly correct errors in our printed media.

All orders are based on our general terms of delivery, which can be reviewed on the websites of our group companies where you place your order. On demand we can also send the general terms of delivery to you.

Siemens, S7-1200 are registered trademarks of Siemens AG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
32758 Detmold, Germany
T +49 5231 14-0
F +49 5231 14-292083
www.weidmueller.com

Personal support can
be found on our website:
www.weidmueller.com/contact

Made in Germany

07/2025/SMM