






The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited.

© Weidmüller Interface GmbH & Co. KG





Customer drawing

LXXX 15.00/04/90FL...




LXXX 15.00/04/90FR...



n = No. of poles
L = 4.8 ±0.35
P = Pitch

GENERAL TOLERANCE:
DIN ISO 2768-m



	9	120	1.372
	8	105	1.313
	7	90	1.254
	6	75	1.195
	5	60	1.136
	4	45	1.77
	3	30	1.18
	2	15	0.59
n	L1[mm]	L1[inch]	

For the mounting of PCBs, it should be noted that the rated data relates only to the PCB components alone. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 60664-1 (VDE 0110). The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 60326-3 very fine line.

Weidmüller PCB components are tested to the IEC 60947-7-4 standard, and are valid for its field of application. Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermal and corrosive stress will be satisfied.

RoHS COMPLIANT

EC00000683 00

Max. nos.

First Issue Date: 14.05.2018

Modification:

Date: 03.12.2018 Name: Xiang, Keqin

Drawn: 03.12.2018 Responsible: Xiang, Keqin

Scale: 1/1 Size: A2 Approved: 04.12.2018 Xu, Shary

Prim PLM Part No.: 004587 Prim ERP Part No.: 1047150000

Weidmüller 46279

Customer drawing

LXXX 15.00/04/90... LEITERPLATTENKLEMME PCB TERMINAL

Product file: 7082 LXXX 15.00