

**WORKPLACE
SOLUTIONS**

Weidmüller 



Workplace Solutions

CA 100 DUO – Semi-automatic stripping and crimping machine

Machining of two cross sections without tool change

The electro-pneumatic CA 100 DUO enables an automatic stripping and crimping of conductors in one step. The stripping- and crimping machine is contributing to a time saving and efficient processing of loose wire end ferrules. In parallel, the machine is offering a high degree of flexibility when processing of two cross sections and not necessary tool change.



Trapezoidal



Insulated ferrules



More information on our Website:
www.weidmueller.com

Your Benefits:

- No tool change necessary when changing cross-sections
- One touch cross-section change
- Reliable processing of various insulation materials
- Separate stripping mode adjustable

Wire-end ferrules with plastic collars

The perfect Duo


- Polypropylene conical entry funnel
- Heat-resistant up to 105°C
- The entry funnel can also be manufactured from a non-flammable material on request

For conductors from 4,0 – 10,0 mm² (AWG 12 – 8)

Material E-Cu. electro-galvanised

Dimensional tolerance acc. to DIN 46228 Part 4

VG* = Military designation acc. to VG 96933-20



Type	Order No.
CA 100 DUO	2740900000

Weidmüller Colour code

Loose packed



Type	Ø mm ²	AWG	L1	L2	D1	D2	S1	S2	Abisolierlänge	Colour	Qty.	Order No.
H4,0/18D GR	4	AWG 12	18,00	10	2,8	4,8	0,2	0,3	12	grey	500	9019190000
H4,0/20D GR	4	AWG 12	20,00	12	2,8	4,8	0,2	0,3	14	grey	500	9019200000
H4,0/26D GR	4	AWG 12	28,00	18	2,8	4,8	0,2	0,3	20	grey	100	9019210000
H6,0/20 SW	6	AWG 10	20,00	12	3,5	6,3	0,2	0,3	14	black	100	0533500000
H6,0/26 SW	6	AWG 12	26,00	18	3,5	6,3	0,2	0,3	20	black	100	0565700000
H10,0/22 EB	10	AWG 7	22,00	12	4,5	7,6	0,2	0,4	15	ivory	100	0534200000
H10,0/28 EB	10	AWG 7	28,00	18	4,5	7,6	0,2	0,4	21	ivory	100	0565800000

DIN Colour code

Loose packed



Type	Ø mm ²	AWG	L1	L2	D1	D2	S1	S2	Stripping length	Colour	VG*	Qty.	Order No.
H4,0/18D GR	4	AWG 12	18,00	10	2,8	4,8	0,2	0,3	12	grey	T 20A 023 A	500	9019190000
H4,0/20D GR	4	AWG 12	20,00	12	2,8	4,8	0,2	0,3	14	grey	T 20A 024 A	500	9019200000
H4,0/26D GR	4	AWG 12	26,00	18	2,8	4,8	0,2	0,3	20	grey	T 20A 025 A	100	9019210000
H6,0/20D GE	6	AWG 10	20,00	12	3,5	6,3	0,2	0,3	14	yellow	T 20A 022 A	100	9019220000
H6,0/26D GE	6	AWG 10	26,00	18	3,5	6,3	0,2	0,3	20	yellow	T 20A 023 A	100	9019230000
H10,0/22D R	10	AWG 7	22,00	12	4,5	7,6	0,2	0,4	15	red	T 20A 024 A	100	9019240000
H10,0/28D R	10	AWG 7	28,00	18	4,5	7,6	0,2	0,4	21	red	T 20A 025 A	100	9019250000

Other Colour code

Loose packed



Type	Ø mm ²	AWG	L1	L2	D1	D2	S1	S2	Stripping length	Colour	Qty.	Order No.
H4,0/18T OR	4	AWG 12	18,00	10	2,8	4,8	0,2	0,3	12	orange	500	9021100000
H4,0/20T OR	4	AWG 12	20,00	12	2,8	4,8	0,2	0,3	14	orange	500	9021110000
H4,0/26T OR	4	AWG 12	26,00	18	2,8	4,8	0,2	0,3	20	orange	100	9021120000
H6,0/20T GN	6	AWG 10	20,00	12	3,5	6,3	0,2	0,3	14	green	100	9021130000
H6,0/26T GN	6	AWG 10	26,00	18	3,5	6,3	0,2	0,3	20	green	100	9021140000
H10,0/22T BR	10	AWG 7	22,00	12	4,5	7,6	0,2	0,4	15	brown	100	9021150000
H10,0/28T BR	10	AWG 7	28,00	18	4,5	7,6	0,2	0,4	21	brown	100	9021160000