





Hinweis / information :
weitere Informationen siehe Zeichnung 34146 /
further informations see drawing 34146

* supply/ equipping without pick & place pad (PPP)

tape width (dimension w) - see order sheet 00
tape Breite W - siehe Blatt 00

tape for pin length 1.5 to 3.5 mm
Tape für Stiftlänge 1.5mm BIS 3.5mm

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

GENERAL TOLERANCE: DIN ISO 2768-mK						Cat.no.: .					
		99546/5 04.12.17 HELIS_MA		01		Weidmüller 		3 29196		32	
		Modification						Drawing no.		Issue no.	
				Date		Name		SL-SMT 3.50/.../180...RL STIFTLEISTE MALE HEADER			
		Drawn		10.06.2008		HELIS_MA					
		Responsible				AMANN_A					
Scale: 2/1		Checked		05.01.2018		HERTEL_S					
Supersedes: .		Approved				LANG_T		Product file: SL-SMT 3.50			
								Sheet 01		of 02 sheets	