

8000057078 PV combiner box thermal report

PV 216S0F0C15V0O1TXPX15PFWW

INPUT DATA


Enclosure model	835 x 635 x 300 mm
Number of MPPT	1
Switch-disconnector model (per MPPT)	400A 8P 1500V (4poles)
Maximum current (per MPPT)	150 A
Number of inputs (per MPPT)	16
Fuse-link model	15A gPV 1500V 10x85mm
Number of Transclinic xi+ devices (per MPPT)	0
Type of mounting	Against wall, all other sides detached
Maximum allowed internal temperature	70 °C
Combined inputs	1
Height (A)	300 mm
Width (B)	635 mm
Depth (C)	835 mm
Effective cooling surface A_e of the enclosure	1,46 m ²

RESULTS

Ambient temperature (no direct sunlight)	59 °C
Rated current per input at 59°C	9,40 A
Power dissipated by components (except wiring)	60 W
Power dissipated by wiring	3 W
Total dissipated power	62 W
Temperature rise, mid height	11 °C
Temperature rise, top	12 °C
Internal temperature, top	71 °C

CURRENT RATINGS

At 35°C	9,40 A
At 40°C	9,40 A
At 45°C	9,40 A
At 50°C	9,40 A



NOTES

Thermal report based on IEC TR 60890 ed2.0

Thermal report does not include the direct sunlight effects