



Ref. Certif. No.

NL-89334

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Terminal block for copper conductors

Name and address of the applicant

Weidmüller Interface GmbH & Co. KG
Klingenbergrasse 16 / 26, 32758 Detmold
Germany

Name and address of the manufacturer

Weidmüller Interface GmbH & Co. KG
Klingenbergrasse 16 / 26, 32758 Detmold
Germany

Name and address of the factory

Note: When more than one factory, please report on page 2

Weidmüller Interface GmbH & Co. KG
Klingenbergrasse 16 / 26, 32758 Detmold
Germany

Additional information on page 2

Ratings and principal characteristics

Ui 400 V - 1000 V, Uimp 4 kV - 8 kV
Rated cross section 1,5 mm² - 240 mm²

Trademark / Brand (if any)

Weidmüller

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

WDU 1.5/ZZ, WDU 1.5/R3.5, WDU 2.5, WDU 4, WDU 6, WDU 10, WDU 16,
WDU 35, WDU 35IK, WDU 50N, WDU 70/95, WDU 120/150, WDU 240

Additional information (if necessary may also be reported on page 2)

Additional information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60947-7-1:2009

As shown in the Test Report Ref. No. which forms part of this Certificate

2199301.53 up to 2199301.62, 2265253.53 and 2276770.50

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
Arnhem, 6825 MJ
Netherlands



Date: 2023-07-13

Signature: H.R.M. Barends



Ref. Certif. No.

NL-89334

Additional factory

Weidmüller Lanskroun, s.r.o.
Dobrovskeho 1115
Lanskroun, 56301
Czech Republic

Weidmüller Interface Romania S. R. L.
Strada 66
Tautii Magheraus, 437345
Romania

Weidmüller Interface (Suzhou) Co. Ltd.
No. 58 Shilin Road
215151 Suzhou Jiangsu
China

EWE s.r.o.
Trebovska 570
Usti Nad Orlici, 562 03
Czech Republic

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
Arnhem, 6825 MJ
Netherlands



Date: 2023-07-13

Signature: H.R.M. Barends