




M 1/1

BEDRUCKUNGSVORLAGE SIEHE ZNG: 43764
PRINT DRAWING NO.: 43764

ORDER NUMBERS SEE SHEET: S 43761

CODING SCHEME SEE SHEET: K 43761

REPRESENTED: BLZ7.62HP/5/180

6	38,10	1,500
5	30,48	1,200
4	22,86	0,900
3	15,24	0,600
2	7,62	0,300
n	L1 [mm]	L1 [Inch]

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermal and corrosive stress will be satisfied.

General tolerance: DIN ISO 2768-mK	.		.		Cat. no.:
	94081/5 02.05.17 HELIS_MA	00	Modification		
				Date	Name
				Drawn	24.04.2017 HELIS_MA
				Responsible	KRUG_M
Scale: 2:1			Checked	11.05.2017 HELIS_MA	
Supersedes: .			Approved	LANG_T	Product file: BLZ/SL 7.62 HP

Weidmüller

3 43761 06

Drawing no. 01 of 02 sheets

BLZ 7.62HP/..180
BUCHSENLEISTE
SOCKET BLOCK

Issue no.

00

7375