

Specification Text - Enclosure, Sheet steel

120 mm x 120 mm x 80 mm ... 250 mm x 400 mm x 130 mm (Hight x Width x Depth)

Specification Text short:

Manufacturer:	Weidmüller
Brand:	Klippon®
Type:	Terminal box, junction box, distribution box
Enclosure range:	Klippon STB
Material:	Sheet Steel, powder coated (RAL 7032)
Lid:	4x captive fixing screws (SW10 Slot)
Ambient temperatures:	-60 °C ≤ Tamb ≤ +120 °C (DIN EN 62208), including aging cycles


Specification Text long:

Manufacturer:	Weidmüller
Brand:	Klippon®
Type:	Terminal box, junction box, distribution box
Enclosure range:	Klippon STB
Description:	Klippon STB 1 MS HT
Article number:	1024970000
Material:	Sheet Steel, powder coated (RAL 7032)
Manufacturing process:	Laser formed from one-piece, edged and welded. Welded joints certified to DVS, DIN EN 15085-2, Cl-2.
Wall thickness:	Enclosure base 1.5 mm / Lid 1.5 mm
IP / NEMA Rating:	IP66 (EN 62208, DIN EN 60529)
Surface:	Powder coated (RAL 7032)
Dimensions (H x W x D):	120 mm x 120 mm x 80 mm
Lid:	4x captive fixing screws (SW10 Slot)
Sealing for lid:	Single (non-jointed) silicon gasket with compression control. Flat (10 mm) seal design so as to prevent damage to the sealing gasket.
Earth bolt:	Internal / external: 1x M6 of stainless steel V4A / 316L / 1.4404, welded; Internal on the lid: 1x M6 of stainless steel V4A / 316L / 1.4404, welded
Enclosure attachment:	4x captive fixing screws (SW10 Slot)
Ambient temperatures:	-60 °C ≤ Tamb ≤ +120 °C (DIN EN 62208)
Impact resistance:	IK 09 (10 J) (DIN EN 50102)

Specification Text - Enclosure, Sheet steel

120 mm x 120 mm x 80 mm ... 250 mm x 400 mm x 130 mm (Height x Width x Depth)

Klippon STB 1



Options:

Label fixing sets:

Stainless steel V4A / 316L / 1.4404, screwed or fixed by rivets. Punched silicon gasket with compression control for the label and its silicon gasket, to ensure the IP rating.

Mounting plates:

DIN rail C type, welded

Earth bolt:

Internal / external: M10 of stainless steel V4A / 316L / 1.4404 or M10 of brass or M6 of stainless steel V4A / 316L / 1.4404 or M6 of brass

Assembly of terminals:

All terminal blocks of type Klippon® Connect. All DIN rails vertical mounting, horizontal mounting as option. Terminal marker horizontal. Hazardous areas: All terminals for intrinsically safe circuits are colored blue, for non-intrinsically safe circuits are colored dark beige. On request: Assembly with control stations (switches, push buttons, lights, indicators).

Certifications:

For assembled resp. empty enclosures

Lloyd's Register

Russian Maritime Register of Shipping

Specification Text - Enclosure, Sheet steel**120 mm x 120 mm x 80 mm ... 250 mm x 400 mm x 130 mm (Hight x Width x Depth)****Weidmüller Interface GmbH & Co. KG**

Postfach 3030

32720 Detmold

Klingenbergstraße 16

32758 Detmold

Phone +49 (0) 5231 14-0

Fax +49 (0) 5231 14-292083

E-Mail info@weidmueller.comInternet www.weidmueller.com

You can find your local contact
on the internet at:

www.weidmueller.com/countries