



conductor
screwdriver
conductor



36	2,345	59,50
34	2,207	56,00
32	2,069	52,50
30	1,931	49,00
28	1,793	45,50
26	1,655	42,00
24	1,517	38,50
22	1,379	35,00
20	1,241	31,50
18	1,103	28,00
16	965	24,50
14	827	21,00
12	689	17,50
10	551	14,00
8	413	10,50
6	275	7,00
n L1[inch] L1 [mm]		

shown: B2L 3.5/08LH QV4 BED

GENERAL TOLERANCE: DIN ISO 2768-mK	Cat. no.:	
	87939/5 03.05.16 HELIS_MA	01
RoHS COMPLIANT	Modification	
	Date	Name
	Drawn 02.07.2007	NICKOL_M
	Responsible	AMANN_A
Scale: 2:1	Checked 13.05.2016	HELIS_MA
Supersedes: .	Approved	HECKERT_M
	Product file: B2L QV	
	Drawing no. 00 of 00 sheets	
	Issue no. 02	

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

B2L 3.50/.../...PRT
BUCHSENLEISTE
SOCKET BLOCK