

Terminal blocks

Simply work more efficiently

Standardised terminal rails for main distribution in buildings



Article No.: 8000122110 - TR BD WPD W/O TS

Pre-equipped terminal block for main distribution with one feed via main line branch terminals (HLAK).

Bill of materials:

- 1 x main line branch terminal; brown; 25 mm ²	(1561120000)
- 1 x main line branch terminal; black; 25 mm ²	(1561100000)
- 1 x main line branch terminal; gray; 25 mm ²	(1560730000)
- 1 x main line branch terminal; blue; 25 mm ²	(1560670000)
- 1 x main line branch terminal; green; 25 mm ²	(1560650000)

Terminal block fixed with rubber ring – without DIN rail.


WPD 101

25 mm²



Width / Height / Depth	mm
max. current / max. conductor	A/mm²
max. clamping range	mm²

17.8 / 49.3 / 55.7
101 / 25
1.5...25



Technical data

Rated data		
Rated voltage		V
Rated current		A
for wire cross-section	25 mm²	mm²
Rated impulse withstand voltage / Pollution severity		
Overvoltage category / UL 94 flammability rating		
Approvals		
Clamped conductors (H05V/H07V)		
Solid / Stranded	25 mm²	mm²
	16 mm²	mm²
Flexible with ferrule	25 mm²	mm²
	16 mm²	mm²
Stripping length / Blade size	25 mm²	mm/-
	16 mm²	mm/-
Tightening torque		Nm
Note		

IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
1000	600		
152	90		
25	AWG 16...4		
8 kV / 3			
III / V-0			
CE   			
Rated connection			
2.5...25 / 2.5...25			
1.5...16 / 1.5...16			
1.5...16			
1.5...10			
19 / M6 (+/- PZ2)			
19 / M6 (+/- PZ2)			
see appendix at the end of the chapter			
I _{max} : 164 A with the connection of 4 x 16 mm²			

Ordering data

Version		
	light grey	
	blue	
	green	
	brown	
	black	
	3x light grey / blue	
	green / 3x light grey / blue	
Note		

Type	Qty.	Order No.
WPD 101 2X25/2X16 GY	5	1560730000
WPD 101 2X25/2X16 BL	5	1560670000
WPD 101 2X25/2X16 GN	5	1560650000
WPD 101 2X25/2X16 BN	5	1561120000
WPD 101 2X25/2X16 BK	5	1561100000

Accessories

End bracket	
	dark beige
	dark beige
Screwdriver	

Type	Qty.	Order No.
WEW 35/2	100	1061200000
AEB 35 SC/1	50	1991920000
SDK PZ2 X 100	1	2749450000