

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Terminal blocks for copper conductors

Name and address of the applicant

Weidmüller Interface GmbH & Co. KG
Klingenbergsstrasse 16 / 26, 32758 Detmold
Germany

Name and address of the manufacturer

Weidmüller Interface GmbH & Co. KG
Klingenbergsstrasse 16 / 26, 32758 Detmold
Germany

Name and address of the factory

 Additional information on page 2Weidmüller Interface GmbH & Co. KG
Klingenbergsstrasse 16 / 26, 32758 Detmold
Germany

Ratings and principal characteristics

1000 Vac / 1500 Vdc , 8 kV / 10 kV, 95 mm², 232 A (A2C 95/120, A2C 95/120-DM)
95 mm² (A2C 95/120 PE)

Trademark (if any)

Weidmüller

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

A2C 95/120, A2C 95/120-DM, A2C 95/120 PE

Additional information (if necessary may also be reported on page 2)

 Additional information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60947-7-1:2009, IEC 60947-7-2:2009

As shown in the Test Report Ref. No. which forms part of this Certificate

2253688.52 and 2253688.53

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051, NL-6825 MJ Arnhem, Netherlands

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Additional factory

Weidmüller Interface

Romania S. R. L.

Strada 66

437345 Tautii Magheraus

Romania

Weidmüller Interface (Suzhou) Co. Ltd.

No. 58 Shilin Road

215151 Suzhou

China

EWE s.r.o.

Trebovska 570

562 03 Usti Nad Orlici,

Czech Republic

Weidmuller Lanskroun, s.r.o.

Dobrovskeho 1115

56301 Lanskroun

Czech Republic

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.

Meander 1051, NL-6825 MJ Arnhem, Netherlands

