


HOLE PATTERN

P = pitch = 10.16
l = pin length
n = no of poles
D = 1.6+0.1

GENERAL TOLERANCE:
DIN ISO 2768-mK

SHOWN: LUP 10.16/04/90V



12	111,76	4,400
11	101,60	4,000
10	91,44	3,600
9	81,28	3,200
8	71,12	2,800
7	60,96	2,400
6	50,80	2,000
5	40,64	1,600
4	30,48	1,200
3	20,32	0,800
2	10,16	0,400
n	L1 [mm]	L1 [inch]

5.0	0.196
3.2	0.125
l	l
[mm]	[inch]

 102478	First Issue Date	03.03.2018	Prim PLM Part No.: 008435	Prim ERP Part No.: 1193000000
			Modification	
			Date	Name
			Drawn	03.03.2018 Administrator
			Responsible	Amann, Alexander
Scale: 2:1	Size: A3	Approved	22.11.2018	Lang, Thomas
Drawings Assembly				

Weidmüller

52588

07

Issue no.

Drawing no.

Sheet 01 of 01 sheets

LUP 10.16/../90V...
LEITERPLATTENKLEMME
PCB TERMINAL

Product file: 7233 LUP 10.16/12.7

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.