

Specification Text - Enclosure, Aluminium

45 mm x 50 mm x 30 mm ... 230 mm x 280 mm x 111 mm (Hight x Width x Depth)

Specification Text short:

Manufacturer: Weidmüller
Brand: Klippon®
Type: Terminal box, junction box, distribution box
Enclosure range: Klippon K
Material: Aluminium AlSi12
Lid: 4x captive fixing screws (Torx-Slot), hinge as option
Ambient temperatures: $-60\text{ °C} \leq T_{amb} \leq +135\text{ °C}$ (IEC 60079-7), including aging cycles


Specification Text long:

Manufacturer: Weidmüller
Brand: Klippon®
Type: Terminal box, junction box, distribution box
Enclosure range: Klippon K
Description: Klippon K41 Ex
Article number: 9526920000
Material: Aluminium AlSi12
Manufacturing process: Die-cast aluminum.
Wall thickness: Enclosure base $\geq 3\text{ mm}$, Draft angle 1 to 2 ° / lid 3 mm
IP / NEMA Rating: IP66, IP 67 (EN 62208, DIN EN 60529, IEC 60079-0) / NEMA 4, 4X (UL 50E, CSA C22.2)
Surface: Natural
Dimensions (H x W x D): 120 mm x 122 mm x 81 mm
Lid: 4x captive fixing screws (Torx-Slot), hinge as option
Sealing for lid: Single (non-jointed) silicon O-ring with compression control, to prevent damage to the sealing gasket
Earth bolt: Internal: Srew connection / External: 1x M4 Earth bolt of stainless steel
Enclosure attachment: 4x captive fixing screws (Torx-Slot)
Ambient temperatures: $-60\text{ °C} \leq T_{amb} \leq +135\text{ °C}$ (IEC 60079-7)
Impact resistance: 7 J (IEC 60079-0)
EMC: Tested and based on VG95373-15:2004-07, methode KS 04B.
Determined shielding effectiveness is in average around 30 dB within the frequency range 100 to 1500 MHz

Specification Text - Enclosure, Aluminium

45 mm x 50 mm x 30 mm ... 230 mm x 280 mm x 111 mm (Hight x Width x Depth)

Klippon K41



Options:

Label fixing sets:

Stainless steel V4A / 316L / 1.4404, screwed or fixed by rivets. Punched silicon gasket with compression control for the label and its silicon gasket, to ensure the IP rating.

Mounting plates:

Galvanized sheet steel

Earth bolt:

Internal / external: M10 of stainless steel V4A / 316L / 1.4404 or M10 of brass or M6 of stainless steel V4A / 316L / 1.4404 or M6 of brass

Wall mounting brackets:

Set with 4 external brackets, stainless steel V2A / 304, 1.4301

Assembly of terminals:

All terminal blocks of type Klippon® Connect. All DIN rails vertical mounting, horizontal mounting as option. Terminal marker horizontal. Hazardous areas: All terminals for intrinsically safe circuits are colored blue, for non-intrinsically safe circuits are colored dark beige. On request: Assembly with control stations (switches, push buttons, lights, indicators).

Specification Text - Enclosure, Aluminium

45 mm x 50 mm x 30 mm ... 230 mm x 280 mm x 111 mm (Hight x Width x Depth)

Certifications: For assembled resp. empty enclosures
ATEX:
II 2G Ex e IIC T6 ... T4 Gb
II 2G Ex ia IIC T6 ... T4 Gb
II 2D Ex tb IIIC T85°C ... T135°C Db
IECEX:
Ex e IIC T6 ... T4 Gb
Ex ia IIC T6 ... T4 Gb
Ex tb IIIC T85°C ... T135°C Db
EAC Ex:
1Ex e IIC T6 ... T4 Gb
1Ex ia IIC T6 ... T4 Gb
Ex tb IIIC T85°C ... T135°C Db
Russian Maritime Register of Shipping
Germanischer Lloyd
cULus
OIT Certification, Russia, Non-Containment, safety-related applications

Weidmüller Interface GmbH & Co. KG

Postfach 3030
32720 Detmold
Klingenbergstraße 16
32758 Detmold
Phone +49 (0) 5231 14-0
Fax +49 (0) 5231 14-292083
E-Mail info@weidmueller.com
Internet www.weidmueller.com

You can find your local contact
on the internet at:
www.weidmueller.com/countries