

# TYPE APPROVAL CERTIFICATE

Certificate no.:  
**TAE000013S**  
Revision No:  
**4**

## This is to certify:

that the Enclosure for Electrical Equipment

with type designation(s)

**Klippon TB Multi Hinge, Klippon TB Quarter Lock, Klippon TB Fixing Screw**

issued to

**Weidmüller Interface GmbH & Co. KG**

**Detmold, Germany**

is found to comply with

**DNV rules for classification – Ships, offshore units, and high speed and light craft**

## Application:

Product(s) approved by this certificate is/are accepted for installation on all vessels classed by DNV.

Degree of protection    **IP66/IP67**  
Vibration class            **A**

Issued at **Hamburg** on **2026-01-07**

This Certificate is valid until **2030-11-25**.

DNV local unit: **Hamburg – CMC North/East**

Approval Engineer: **Torsten Dzillak**

for DNV



This document has been digitally signed and will  
therefore not have handwritten signature

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid.  
The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.

LEGAL DISCLAIMER: Unless otherwise stated in the applicable contract with the holder of this document, or following from mandatory law, the liability of DNV AS, its parent companies and their subsidiaries as well as their officers, directors and employees ("DNV") arising from or in connection with the services rendered for the purpose of the issuance of this document or reliance thereon, whether in contract or in tort (including negligence), shall be limited to direct losses and under any circumstance be limited to USD 300 000.

## Product description

Type Klippon TB Multi Hinge (Stainless steel enclosures for use in areas exposed to explosion hazards)

|                       |  |
|-----------------------|--|
| Size                  | Height 150 – 1250mm<br>Width 150 – 1000mm<br>Depth 80 - 300 mm |
| Material              | Stainless Steel 1.4404 (1.4301),<br>Mild Steel (1.0330)        |
| Material thickness    | 1,5 mm , gland plates min 3mm                                  |
| Finish                | Stainless Steel: electrochemical polish, nature with finish    |
| Gasket                | Silicon  |
| Ingress protection    | IP 66/67 as per IEC 60529                                      |
| Temperature           | -60°C to + 135°C (IP 66)<br>-60°C to + 105°C (IP 67)           |
| Type of Ex protection | Ex e, Ex tb as per certificate IECEx IBE 14.0004U              |

Type Klippon TB Quarter Lock (Stainless steel enclosures for use in areas exposed to explosion hazards)

|                       |  |
|-----------------------|--|
| Size                  | Height 150 – 980mm<br>Width 150 – 740mm<br>Depth 80 - 300 mm |
| Material              | Stainless Steel 1.4404 (1.4301),<br>Mild Steel (1.0330)      |
| Material thickness    | 1,5 mm , gland plates min 3mm                                |
| Finish                | Stainless Steel: electrochemical polish, nature with finish  |
| Gasket                | Silicon  |
| Ingress protection    | IP 66 as per IEC 60529                                       |
| Temperature           | -60°C to + 135°C (IP 66)                                     |
| Type of Ex protection | Ex e, Ex tb as per certificate IECEx IBE 14.0004U            |

Type Klippon TB Fixing Screw (Stainless steel enclosures for use in areas exposed to explosion hazards)

|                       |  |
|-----------------------|--|
| Size                  | Height 150 – 1500mm<br>Width 150 – 1000mm<br>Depth 80 - 300 mm |
| Material              | Stainless Steel 1.4404 (1.4301),<br>Mild Steel (1.0330)        |
| Material thickness    | 1,5 mm , gland plates min 3mm                                  |
| Finish                | Stainless Steel: electrochemical polish, nature with finish    |
| Gasket                | Silicon  |
| Ingress protection    | IP 66/67 as per IEC 60529                                      |
| Temperature           | -60°C to + 135°C (IP 66)<br>-60°C to + 105°C (IP 67)           |
| Type of Ex protection | Ex e, Ex tb as per certificate IECEx IBE 14.0004U              |

## Application/Limitation

Stainless steel enclosures for use in areas exposed to explosion hazards.  
Operating instruction of the manufacturer to be observed.

## Type Approval documentation

Weidmüller test reports: LAB 14144 (2006-08-01), LAB 14145 (2006-08-02), LAB 16307 (2010-04-27), LAB 16308 (2010-04-27), LAB 16383 (2010-06-18), LAB 16387 (2010-06-21)

AKUVIB test report no. 2010-03-0364-VU (2010-09-21)

IIECEx Certificate of Conformity no. IBE 14.0004U (2014-05-05)

Assembly guideline – empty enclosures R.T.Nr. 20000560000/00/02.15

Drawing no. 4 59379 (2015-03-17)

Technical Information ATEX/IIECEx Certification Update for the Klippon TB range

Type Approval Assessment Report ((2016-03-16))

Type Approval Assessment Report ((2025-10-23))

## Tests carried out

Type tests in accordance with EN 62208, vibration test according to EN 60068-2-64, EN 60068-2-27, IEC 60529:2001

## Place of manufacture

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 16  
32758 Detmold, GERMANY

## Marking of product

The products to be marked with:

- manufacture name
- device name
- serial number

## Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the Type approval are complied with and that no alterations are made to the product design or choice of materials.

The main elements of the assessment are:

- Inspection on factory samples, selected at random from the production line (where practicable)
- Results from Routine Tests (RT) checked (if not available tests according to RT to be carried out)
- Review of type approval documentation
- Review of possible change in design, materials and performance
- Ensuring traceability between manufacturer's product type marking and Type Approval Certificate.

Periodical assessment is to be performed after 2 years and after 3.5 years. A renewal assessment will be performed at renewal of the certificate.

END OF CERTIFICATE