

Document No. **UKCA PA53 210628 003 ISS 01**

Manufacturer **Weidmüller Interface GmbH & Co. KG**

Address **Klingenbergstr. 26  
32758 Detmold, Germany**

Object of the declaration **VPU AC II US Series**

☒ Continued on page 2

The manufacturer attests, in sole-responsibility, that the object of the declaration described above is in conformity with the essential requirements of directive(s):

|                                                                                                                                                                                         |              | Directive                              |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|----------------------------------------|
| <input checked="" type="checkbox"/> The Electrical Equipment (Safety) Regulations 2016                                                                                                  | SI 2016/1101 | SI2019/696(Schedule23)<br>SI 2020/1460 |
| <input type="checkbox"/> The Electromagnetic Compatibility Regulations 2016                                                                                                             | SI 2016/1091 | SI2019/696(Schedule20)<br>SI 2020/1460 |
| <input type="checkbox"/> The supply of Machinery (Safety) Regulations 2008                                                                                                              | SI 2008/1597 | SI2019/696(Schedule12)<br>SI 2020/1460 |
| <input type="checkbox"/> The Radio Equipment Regulations 2017                                                                                                                           | SI 2017/1206 | SI2019/696(Schedule29)<br>SI 2020/1460 |
| <input checked="" type="checkbox"/> The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 RoHS                             | SI 2012/3032 | SI2019/188                             |
| <input type="checkbox"/> The Equipment and Protective Systems Intended for Use in Potentially Explosive Atmospheres Regulations 2016<br>Marking (Equipment Group, Category, Atmosphere) | SI 2016/1107 | SI2019/696(Schedule25)<br>SI 2020/1460 |

References to the relevant EN or BSEN designated standards used, or references to the specifications, in relation to which conformity is declared:

**EN 61643-11:2012 + A11:2018**

Document No. **UKCA PA53 210628 003 ISS 01**

Object of the declaration (continued from page 1)

|            |                            |
|------------|----------------------------|
| 2726810000 | VPU AC II US 0 60/50       |
| 2736210000 | VPU AC II US 1 60/50       |
| 2736270000 | VPU AC II US 1 R 60/50     |
| 2736280000 | VPU AC II US 2 60/50       |
| 2730790000 | VPU AC II US 2 R 60/50     |
| 2730440000 | VPU AC II US 0 120/50      |
| 2730450000 | VPU AC II US 1 120/50      |
| 2730460000 | VPU AC II US 1 R 120/50    |
| 2730470000 | VPU AC II US 2 120/50      |
| 2730480000 | VPU AC II US 2 R 120/50    |
| 2730490000 | VPU AC II US 4 120/50      |
| 2730500000 | VPU AC II US 4 R 120/50    |
| 2730510000 | VPU AC II US 3 120/50      |
| 2730520000 | VPU AC II US 3 R 120/50    |
| 2730530000 | VPU AC II US 0 240/50      |
| 2736300000 | VPU AC II US 1 240/50      |
| 2736310000 | VPU AC II US 1 R 240/50    |
| 2736320000 | VPU AC II US 2 240/50      |
| 2736330000 | VPU AC II US 2 R 240/50    |
| 2736340000 | VPU AC II US 1+1 240/50    |
| 2736350000 | VPU AC II US 1+1 R 240/50  |
| 2736360000 | VPU AC II US 3+1 240/50    |
| 2736390000 | VPU AC II US 3+1 R 240/50  |
| 2736400000 | VPU AC II US 4 240/50      |
| 2736410000 | VPU AC II US 4 R 240/50    |
| 2730540000 | VPU AC II US 3 240/50      |
| 2730550000 | VPU AC II US 3 R 240/50    |
| 2730800000 | VPU AC II US 1 N-PE 240/65 |
| 2736170000 | VPU AC II US 0 N-PE 240/65 |
| 2730690000 | VPU AC II US 0 400/50      |
| 2730700000 | VPU AC II US 1 400/50      |

|            |                             |
|------------|-----------------------------|
| 2736170000 | VPU AC II US 1 R 400/50     |
| 2730720000 | VPU AC II US 3 400/50       |
| 2730730000 | VPU AC II US 3 R 400/50     |
| 2730740000 | VPU AC II US 4 400/50       |
| 2730750000 | VPU AC II US 4 R 400/50     |
| 2730760000 | VPU AC II US 0 600/35       |
| 2736420000 | VPU AC II US 1 R 600/35     |
| 2736430000 | VPU AC II US 2 R 600/35     |
| 2730780000 | VPU AC II US 3 R 600/35     |
| 2730770000 | VPU AC II US 4 R 600/35     |
| 2730560000 | VPU AC II US 0 277/50       |
| 2730570000 | VPU AC II US 1 277/50       |
| 2730580000 | VPU AC II US 1 R 277/50     |
| 2730590000 | VPU AC II US 3 277/50       |
| 2730600000 | VPU AC II US 3 R 277/50     |
| 2730610000 | VPU AC II US 4 277/50       |
| 2730620000 | VPU AC II US 4 R 277/50     |
| 2730630000 | VPU AC II US 2 277/50       |
| 2730640000 | VPU AC II US 2 R 277/50     |
| 2730650000 | VPU AC II US 1+1 277/50     |
| 2730660000 | VPU AC II US 1+1 R 277/50   |
| 2730670000 | VPU AC II US 3+1 277/50     |
| 2730680000 | VPU AC II US 3+1 R 277/50   |
| 2736440000 | VPU AC II US 3+1 R 240/50 Y |
| 2736450000 | VPU AC II US 3 R 240/50 Y   |
| 2736460000 | VPU AC II US 1+1 R 240/50 Y |
| 2736470000 | VPU AC II US 1 R 240/50 Y   |
| 2736480000 | VPU AC II US 2 R 240/50 Y   |
| 2736490000 | VPU AC II US 4 R 240/50 Y   |
| 2736500000 | VPU AC II US 0 240/50 Y     |
| 2736520000 | VPU AC II US 0 N-PE 240 Y   |

Detmold, 09.08.2021

place, date

legally binding signature

Thomas Peter Vice President Business Unit Digital Signaling &amp; Protection

name and function

This declaration certifies compliance with the indicated directive but no warranty of properties. The safety instructions of the accompanying product documentation shall be observed.