

CERTIFICATE

Issued to:
Applicant:
Weidmüller Interface GmbH & Co. KG
Klingenbergstrasse 16
32758 Detmold, Germany

Licensee:
Weidmüller Interface GmbH & Co. KG
Klingenbergstrasse 16
32758 Detmold, Germany

Product : Terminal blocks for copper conductors
Trade name(s) : Weidmüller
Type(s)/model(s) : WDU 4 SL, WDU 4 SL/EN, WDU 4 SL/EN BL, WDU 4 SL/EN SW, WDU 4 SL BL and WDU 4 SL STB 8.5

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 60947-7-1:2009
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 900119


DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration of the KEMA-KEUR certification agreement and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 14 July 2020 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-114605

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



M. Triulzi
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: Terminal blocks for copper conductors
Trade name(s)	: Weidmüller
Type(s)/model(s)	: WDU 4 SL, WDU 4 SL/EN, WDU 4 SL/EN BL, WDU 4 SL/EN SW, WDU 4 SL BL and WDU 4 SL STB 8.5
Rated impulse withstand voltage	: 6 kV
Pollution degree	: 2
Conventional free air thermal current	: 32 A unprepared conductors 24 A cable lugs
Rated cross section	: 4 mm ²
Rated connecting capacity	: 0,5 mm ² - 6 mm ² rigid (solid) 1 conductor 0,5 mm ² - 4 mm ² flexible 1 conductor 0,5 mm ² - 1,5 mm ² rigid (solid) 2 conductor 0,5 mm ² - 1,5 mm ² flexible 2 conductor cable lugs 0,5 mm ² - 2,5 mm ² flexible 1 cable lug cable lugs 0,5 mm ² - 2,5 mm ² flexible 2 cable lugs
Tightening torque	: 0,5 Nm
Cable lugs	: 0,5 mm ² : cable lugs type HBT1.5-3.0RT 2,5 mm ² : cable lugs type HBT2.5-3.0BL endplate type WAP 2,5-10 4-6 should be used at each terminal block if cable lugs are used

Product data – type WDU 4 SL

Rated insulation voltage	: 630 V
Mounting rail	: top hat rail 35 mm
Description	: Feed-through terminal block, 1-pole with 2 screw-type clamping units, colour beige

Product data – type WDU 4 SL BL

Rated insulation voltage	: 630 V
Mounting rail	: top hat rail 35 mm
Description	: Feed-through terminal block, 1-pole with 2 screw-type clamping units, colour blue

Product data – type WDU 4 SL STB 8.5

Rated insulation voltage	: 400 V
Mounting rail	: top hat rail 35 mm
Description	: Feed-through terminal block, 1-pole with 2 screw-type clamping units, colour beige, with connector

Product data – type WDU 4 SL/EN

Rated insulation voltage	: 630 V
Mounting rail	: top hat rail 35 mm and G-profile 32 mm
Description	: Feed-through terminal block, 1-pole with 2 screw-type clamping units, colour beige

Product data – type WDU 4 SL/EN BL

Rated insulation voltage	: 630 V
Mounting rail	: top hat rail 35 mm and G-profile 32 mm
Description	: Feed-through terminal block, 1-pole with 2 screw-type clamping units, colour blue

Product data – type WDU 4 SL/EN SW

Rated insulation voltage	: 630 V
Mounting rail	: top hat rail 35 mm and G-profile 32 mm
Description	: Feed-through terminal block, 1-pole with 2 screw-type clamping units, colour black

TESTS

Test requirements

EN 60947-7-1:2009

Test result

The test results are laid down in DEKRA test file 223960600.

Conclusion

The examination proved that all requirements were met.

Factory location

Weidmüller Interface GmbH & Co. KG
Klingenbergstrasse 16
32758 Detmold, Germany