



SHOWN: SU 10.16IT/04/90MLSF4 3.5 AG BK BX SO

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

General tolerance: DIN ISO 2768-mK		Cat. no.:	
	94698/5 12.06.17 HELIS_MA	00	
Modification			
	Date	Name	
Drawn	18.01.2011	LUETZ_G	
Responsible		KRUG_M	
Scale: 2/1	Checked	13.06.2017	HELIS_MA
Supersedes: .	Approved	LANG_T	Product file: BUZ/SU10.16HP_MF
		3 534 24 01	Drawing no. 01 of 01 sheets

SU 10.16IT/..90MLSF...SO
STIFTLEISTE
MALE HEADER