





The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited. Offenders will be held liable for the payment of damages. Wedmueler exclusively reserves the right to file for patients, utility models or designs.

© Weidmüller Interface GmbH & Co. KG




SHOWN: SL 3.50/04/90G

$$\begin{aligned}
 P &= 3.50 \text{ Raster Pitch} \\
 D &= 01,3^{+0.1}_{\phi 0.051''^{+0.1}} \\
 d &= 1,2\text{mm oktogonal} \\
 &\quad 0.047'' \text{ octogonal}
 \end{aligned}$$

24	80.5	
23	77.0	
22	73.5	
21	70.0	
20	66.5	
19	63.0	+/- 0.2
18	59.5	
17	56.0	
16	52.5	
15	49.0	
14	45.5	
13	42.0	
12	38.5	+/- 0.15
11	35.0	
10	31.5	
9	28.0	
8	24.5	
7	21.0	
6	17.5	+/- 0.1
5	14.0	
4	10.5	
3	7.0	
2	3.5	
pin length l/ Stiftlänge l	tolerance/ Toleranz	
n	Polzahl/ no of poles	L1
		Toleranz/ tolerance l1

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine

Weidmueller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.



Weidmüller 

Drawing no. Issue no.
Sheet 02 of 03 sheets

SL 3.50/../90...
STIFTLEISTE
MALE HEADER