

# CERTIFICATE

DEKRA

Issued to:

Applicant:  
**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstrasse 16  
32758 Detmold, Germany

Licensee:  
**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstrasse 16  
32758 Detmold, Germany

Product : Protective terminal block for copper conductors  
Trade name(s) : WEIDMÜLLER  
Type(s)/model(s) : AKE 2.5 and AKE 4

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 60947-7-2:2009
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 900119

DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration of the KEMA-KEUR certification agreement and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 26 March 2018 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-100029

DEKRA Certification B.V.



drs. G.J. Zoetbrood  
Managing Director



Jens Marggraf  
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE  
DUTCH ACCREDITATION  
COUNCIL



**SPECIFICATION OF THE CERTIFIED PRODUCT****Product data**

Product	: Protective terminal block for copper conductors
Trade name(s)	: WEIDMÜLLER
Type(s)/model(s)	: AKE 2.5 and AKE 4
Material	: PA 66
Method of mounting	: top hat rail 15 mm
Description	: protective terminal block with screw-type clamping units, 1-pole, with 2 clamping units per pole

**Product data – type AKE 2.5**

Rated cross-section	: 2,5 mm <sup>2</sup>
Rated connecting capacity	: 0,5 mm <sup>2</sup> - 4 mm <sup>2</sup> rigid or flexible
Torque	: 0,4 Nm - 0,6 Nm clamping unit and support
PE or PEN functions	: PE

**Product data – type AKE 4**

Rated cross-section	: 4 mm <sup>2</sup>
Rated connecting capacity	: 0,5 mm <sup>2</sup> - 4 mm <sup>2</sup> rigid or flexible
Torque	: 0,5 Nm - 1 Nm clamping unit and support
PE or PEN functions	: PE

**TESTS****Test requirements**

EN 60947-7-2:2009

**Test result**

The test results are laid down in DEKRA test file 219930900.

**Conclusion**

The examination proved that all requirements were met.

**Factory location**

Weidmüller Interface GmbH & Co. KG  
Klingenbergrasse 16  
32758 Detmold, Germany