

## 8000069110 PV combiner box thermal report

PV 40201S2V4C2A0ES

### INPUT DATA


Enclosure model	847 x 636 x 300 mm
Number of MPPT	1
Switch-disconnector model (per MPPT)	no switch-disconnector
Maximum current (per MPPT)	272 A
Number of inputs (per MPPT)	2
Fuse-link model	160A gG NH1
Number of Transclinic xi+ devices (per MPPT)	0
Type of mounting	Against wall, all other sides detached
Maximum allowed internal temperature	70 °C
Combined inputs	1
Height (A)	847 mm
Width (B)	636 mm
Depth (C)	300 mm
Effective cooling surface $A_e$ of the enclosure	1,48 m <sup>2</sup>

### RESULTS

Ambient temperature (no direct sunlight)	35 °C
Rated current per input at 35°C	136,00 A
Power dissipated by components (except wiring)	38 W
Power dissipated by wiring	43 W
Total dissipated power	81 W
Temperature rise, mid height	14 °C
Temperature rise, top	18 °C
Internal temperature, top	53 °C

### CURRENT RATINGS

At 35°C	136,00 A
At 40°C	136,00 A
At 45°C	136,00 A
At 50°C	136,00 A



### NOTES

Thermal report based on IEC TR 60890 ed2.0

Thermal report does not include the direct sunlight effects