




The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited.


Offenders will be held liable for the payment of damages. Weidmüller exclusively reserves the right to file for patents, utility models or designs.

© Weidmüller Interface GmbH & Co. KG




BL 3.50/04/180F






BL 3.50/04/180






BL 3.50/04/180LH




BL 3.50/04/180LR



BL 3.50/04/180LR REDESIGN



ALLGEMEINGEÜLTIGE KUNDENZEICHNUNG, AKTUELLER STAND NUR AUF ANFRAGE
GENERAL CUSTOMER DRAWING, TOPICAL VERSION ONLY IF REQUIRED



MIN. FRONT PLATE CUT-OUT

P = 3.50 RASTER PITCH

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermal and corrosive stress will be satisfied.

24	80.5	3.169
23	77.0	3.032
22	73.5	2.894
21	70.0	2.756
20	66.5	2.618
19	63.0	2.480
18	59.5	2.343
17	56.0	2.205
16	52.5	2.067
15	49.0	1.929
14	45.5	1.791
13	42.0	1.654
12	38.5	1.516
11	35.0	1.378
10	31.5	1.240
9	28.0	1.102
8	24.5	0.965
7	21.0	0.827
6	17.5	0.689
5	14.0	0.551
4	10.5	0.413
3	7.0	0.276
2	3.5	0.138

n POLZAHL L1 L1
POLES [mm] [inch]

Cat. no.: 3 19675

36

Drawing no.

Sheet 00 of 00 sheets

GENERAL TOLERANCE:
DIN ISO 2768-m

RoHS
COMPLIANT

103300/5
17.05.18 HELIS_MA 01

Modification

Weidmüller

3 19675

36

BL 3.50/..180

BUCHSENSTECKER
FEMALE PLUG

In Prüfung /
Verification /

Date

Name

Drawn

02.09.2008

HELIS_MA

Responsible

AMANN_A

Scale: 5/1

Checked

Supersedes: ..

Approved

LANG_T

Product file: BL 3.50

7382