

**INSTALLATION INSTRUCTIONS  
& CONDITIONS FOR SAFE USE** II 3 G Ex ec II C Gc**Modular TERMINAL Blocks: A- Series****TÜV 17 ATEX 8063 U  
IECEx TUR 17.0029 U****Standards:**EN IEC 60079-0:2018 and EN IEC 60079-7:2015 A1:2018  
IEC 60079-0: 7th Edition and IEC 60079-7: 5.1th Edition**Modular Terminal Blocks: AAP21 4 LI...**

Version:	AAP21 4 LI RD*	Order No
		2428930000

in conjunction with:

AAP21 4 DT*	2428980000
AAP21 4 FS*	2428950000
AAP21 4 FS 10-36V*	2458990000
AAP21 4 FS 30-70V*	2460200000
AAP21 4 FS 60-150V*	2460190000
AAP21 4 FS 100-250V*	2460180000
AAP21 10 LO RD*	2428910000
AAP21 10 FE*	2428920000

**Accessories:**

end plate	Type	Order No
end bracket	AEP AP21*	2429020000
	AEB 35 SC/1*	1991920000

**Terminal rail**

TS 35/... acc.to DIN EN 60715

**Cross-connection**

Plugable	Order No
ZQV 4N/2*	1527930000
ZQV 4N/3*	1527940000
ZQV 4N/4*	1527970000
ZQV 4N/5*	1527980000
ZQV 4N/6*	1527990000
ZQV 4N/7*	1528020000
ZQV 4N/8*	1528030000
ZQV 4N/9*	1528070000
ZQV 4N/10*	1528090000

**Insulation material:**

- Type Wemid
- Tracking resistance (A) to IEC 60112
- Flammability class to UL 94 CTI  $\geq$  600  
V0
- Operating temperature range -60°C...+130°C (insulating material limit)

\* in all colours

**Technical data according to IEC/EN 60079-7 (increased safety "ec"):**

	<b>AAP21 10 LO...</b>	<b>AAP21 10 FE</b>	
- Rated voltage	250 V	250 V	
- Rated current	57 A / $\Delta T < 40$ K		
- Contact resistance with rated conductor	0,4 mΩ	0,5 mΩ	
- Rated conductor cross section	10 mm <sup>2</sup>	10 mm <sup>2</sup>	
- Conductor cross section solid	0,5 -10mm <sup>2</sup>	0,5 -10mm <sup>2</sup>	
- Conductor cross section stranded	0,5 - 10mm <sup>2</sup>	0,5 - 10mm <sup>2</sup>	
- Conductor cross section flexible	0,5 - 10mm <sup>2</sup>	0,5 - 10mm <sup>2</sup>	
- cross section, American Wire Gauge	20 - 6 AWG	20 - 6 AWG	
- Stripping length	18 mm	18 mm	
	<b>AAP21 4 LI...</b>	<b>AAP21 4 FS</b>	<b>AAP21 4 DT</b>
- Rated voltage	250 V	250 V	250 V
- Rated current	32 A / $\Delta T < 40$ K	6,3 A / $\Delta T < 40$ K	20 A / $\Delta T < 40$ K
- Contact resistance with rated conductor	0,3 mΩ	4,5 mΩ	1,3 mΩ
		with dummy fuse link no. 2	
- Rated conductor cross section	4 mm <sup>2</sup>	4 mm <sup>2</sup>	4 mm <sup>2</sup>
- Conductor cross section solid	0,5 - 4mm <sup>2</sup>	0,5 - 4mm <sup>2</sup>	0,5 - 4mm <sup>2</sup>
- Conductor cross section stranded	0,5 - 4mm <sup>2</sup>	0,5 - 4mm <sup>2</sup>	0,5 - 4mm <sup>2</sup>
- Conductor cross section flexible	0,5 - 4mm <sup>2</sup>	0,5 - 4mm <sup>2</sup>	0,5 - 4mm <sup>2</sup>
- cross section, American Wire Gauge	26 - 12 AWG	26 - 12 AWG	26 - 12 AWG
- Stripping length	12 mm	12 mm	12 mm

**Service life acc. to IEC 60947-7-1**

- max. no. of actuations	50 cycles
--------------------------	-----------

**Allocated currents of AAP21 10 LO... combination with:**


AAP21 10 LO...	57 A / $\Delta T < 40$ K	
AAP21 4 LI...	57 A / $\Delta T < 40$ K	distribution terminals $\geq 2$
AAP21 4 DT	57 A / $\Delta T < 40$ K	distribution terminals $\geq 3$
AAP21 4 FS	31,5 A / $\Delta T < 40$ K	distribution terminals $\geq 5$

**IECEx / ATEX Terminal and Cross-Connection Arrangements:****Max voltage data according to IEC/EN 60079-7 (increased safety "ec"):****Application Case****A - Continuous feed in with Supply terminal and share with distribution terminal blocks** $I_{max}$ :

250 V

AAP21 10 LO.../ 3 x AAP21 4 LI...

20 A



250 V

6,3 A



250 V

AAP21 10 LO.../ AAP21 4 FS / 3 x AAP21 4 LI...

Please attend the allocated current in the technical data above.

Information for further cross-connector arrangements will be provided on request.

**Mounting instructions:**

The Feed-through terminals of the A-series are suitable for application in enclosures in atmospheres with flammable gases or combustible dust. For use in flammable gases these enclosures must satisfy the requirements according to IEC/EN60079-0 and IEC/EN60079-7. For use in combustible dust these enclosures must satisfy the requirements according to IEC/EN60079-0 and IEC/EN60079-31.

In combination with other terminal block series and sizes and if other accessories are used, the applicable creepage and clearance distances shall be met.

Regarding the use of accessories the instructions of the manufacturer must be followed.

**Schedule of Limitations:**

The Feed-through terminal blocks are suitable for use in enclosures in atmospheres with flammable gases or combustible dust. For flammable gases these enclosures must satisfy the requirements according to IEC/EN 60079-0 and IEC/EN60079-7. For combustible dust these enclosures must satisfy the requirements according to IEC/EN 60079-31.

The enclosure shall be constructed to block all sun and UV light from affecting the terminal blocks. The terminal blocks shall be placed inside a suitable certified IP54 enclosure in type of protection "e" for gas atmosphere. For dust atmosphere the terminal blocks shall be mounted inside a suitable certified enclosure (IEC/EN60079-31) in type of protection "t".

Under normal operating conditions the temperature rise of the terminal blocks is maximum 40 K, measured at the maximum permitted rated current. Due to the above mentioned, the terminal blocks may be used in apparatus of temperature classes T6..T1 as long as the terminal block ambient temperature range is not exceeded. No part of terminal block must exceed 130 °C under any condition.

T6 (- 60°C ... +40 °C)

T5 (- 60°C ... +55 °C)

T4 (- 60°C ... +90 °C)

**WARNING** – Do not remove or replace the test disconnect switch (AAP 21 4 DT) when energized!  
– Do not remove or replace the test fuse disconnect switch (AAP 21 4 FS) when energized!

When using the types of disconnect terminals especially with other terminal blocks series or sizes or accessories the requirements for clearance and creepage distances of IEC/EN 60079-7 must be maintained. Regarding the use of covers, cross-connectors and end brackets the instructions of the manufacturer must be followed.

For cross connection accessories current rating, resistance across the terminal please refer to the table under "Technical data" above.

No other wire sizes or types than the ones specified in instructions must be used. The terminal blocks must either be mounted next to another block of the same type and size or with an end plate.

If smaller conductor cross sections than the rated conductor cross sections are used, then the corresponding lower current shall be stated in the Certificate of the complete apparatus.



- Cross connections with blank ends shall not be used.
- Manually cut cross connections shall not be used.

**Essential Health and Safety Requirements:**

Concerning ESRs this Schedule verifies compliance with the Annex II of ATEX directive only. By placing the product on the market, the manufacturer declares compliance with other relevant Directives, and all other safety related requirements including those of Annex II of this Directive.