



Product Service

CERTIFICATE

No. B 033299 0488 Rev. 00

Holder of Certificate: Weidmüller Interface GmbH & Co. KG

Klingenbergsstr. 26
32758 Detmold
GERMANY

Certification Mark:



Product:

Switching power supply unit (DIN-Rail Power Supply)

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition the certification holder must not transfer the certificate to third parties. See also notes overleaf.

Test report no.: 682102001400

Valid until: 2025-04-14

Date: 2020-04-15


(Yager Bi)



Product Service

C E R T I F I C A T E

No. B 033299 0488 Rev. 00

Model(s): PRO ECO 72W 12V 6A, PRO ECO 72W 24V 3A

Brand Name: Weidmüller

Weidmüller 

Parameters:

Rated Input : 100-240VAC, 50/60Hz, 2-1A or 120-340VDC, 0.8-0.3A

Rated Output : 12VDC, 6A for PRO ECO 72W 12V 6A; 24VDC, 3A for PRO ECO 72W 24V 3A

Protection Class : I

Degree of Protection : IPX0

Remarks:

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Refer to the installation and operating instruction from manufacturer for the details of loading condition and input voltage or operating temperature.
- Clearance was evaluated for operating altitude up to 5000m above sea level.
- The AC input tolerance of the power supply is 85-264VAC. DC input tolerance is 80-370VDC and should be derived by external bridge rectifier from AC mains supply.
- These power supplies are designed to be protectively earthed. Earthing connection and continuity test shall be checked in end product.
- Built-in type equipment, suitable enclosure should be provided by end system.
- When installing the power supply, keep min. 5cm distance for bottom openings for ventilation.

Tested according to: EN 62368-1:2014/A11:2017

Production 057937

Facility(ies):