



Product Service

Attestation of Conformity

No. N8A 18 04 33299 388

Holder of Certificate: Weidmüller Interface GmbH & Co. KG
Klingenbergstr. 16
32758 Detmold
GERMANY

Product: Switching power supply unit
(Switching Power Supply)

This Attestation of Conformity is issued on a voluntary basis according to the Low Voltage Directive 2014/35/EU relating to electrical equipment designed for use within certain voltage limits. It confirms that the listed equipment complies with the principal protection requirements of the directive and is based on the technical specifications applicable at the time of issuance. It refers only to the particular sample submitted for testing and certification. See also notes overleaf.

Test report no.: 6821017057502

Date, 2018-05-16


(Yager Bi)



After preparation of the necessary technical documentation as well as the EU conformity declaration the required CE marking can be affixed on the product. That declaration of conformity is issued under the sole responsibility of the manufacturer. Other relevant EU-directives have to be observed.

Page 1 of 2



Product Service

Attestation of Conformity
No. N8A 18 04 33299 388

Model(s): PRO TOP1 120W 24V 5A, PRO TOP1 120W 24V 5A F,
PRO TOP1 120W 24V 5A EX, PRO TOP1 120W 12V 10A,
PRO TOP1 120W 12V 10A F, PRO TOP1 120W 12V 10A EX

Brand: Weidmüller

Parameters:

Rated Input :	100-240VAC, 50/60Hz, 2.0-1.0A or 120-340VDC, 2.0-0.6A
Rated Output :	24VDC, 5A (For models: PRO TOP1 120W 24V 5A, PRO TOP1 120W 24V 5A F, PRO TOP1 120W 24V 5A EX)
	12VDC, 10A (For models: PRO TOP1 120W 12V 10A, PRO TOP1 120W 12V 10A F, PRO TOP1 120W 12V 10A EX)
Construction :	Built-in
Protection Class :	I
Degree of Protection :	IPX0
Remarks:	<ul style="list-style-type: none">- When installing the equipment, all requirements of the mentioned standard must be fulfilled.- Refer to the installation and operating instruction from manufacturer for the details of loading condition and operating temperature.- Clearance was evaluated for operating altitude up to 5000m above sea level.- Built-in type equipment, suitable enclosure should be provided in end system.- The DC input of these power supplies shall be derived from the end system of maximum 240VAC mains supply.

Tested according to: EN 62368-1:2014/A11:2017