



36	2,345	59,50
34	2,207	56,00
32	2,069	52,50
30	1,931	49,00
28	1,793	45,50
26	1,655	42,00
24	1,517	38,50
22	1,379	35,00
20	1,241	31,50
18	1,103	28,00
16	965	24,50
14	827	21,00
12	689	17,50
10	551	14,00
8	413	10,50
6	275	7,00
n L1[inch] L1 [mm]		

shown: B2L 3.5/08QV4 BED

GENERAL TOLERANCE: DIN ISO 2768-mK		Cat. no.:	
 87939/5 03.05.16 HELIS_MA 01			
Modification			
	Date	Name	
	Drawn	02.07.2007 NICKOL_M	
	Responsible	AMANN_A	
	Scale: 2:1	Checked	13.05.2016 HELIS_MA
	Supersedes:	Approved	HECKERT_M
		Product file: B2L QV	

Weidmüller 
Drawing no. 3 39691 02
Issue no. Sheet 00 of 00 sheets

B2L 3.50/.../...PRT
BUCHSENLEISTE
SOCKET BLOCK

7367

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.