


WEITERGABE SOWIE Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.  
ZuWiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksunterzeichnung vorbehalten.  
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.  
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. ALL RIGHTS RESERVED IN THE EVENT OF THE GRANT OF A PATENT, UTILITY MODEL OR DESIGN.



DIE DEUTSCHE VERSION IST VERBINDLICH  
THE GERMAN VERSION IS BINDING

|    |         |           |
|----|---------|-----------|
| 24 | 116,84  | 4,600     |
| 23 | 111,76  | 4,400     |
| 22 | 106,68  | 4,200     |
| 21 | 101,60  | 4,000     |
| 20 | 96,52   | 3,800     |
| 19 | 91,44   | 3,600     |
| 18 | 86,36   | 3,400     |
| 17 | 81,28   | 3,200     |
| 16 | 76,20   | 3,000     |
| 15 | 71,12   | 2,800     |
| 14 | 66,04   | 2,600     |
| 13 | 60,96   | 2,400     |
| 12 | 55,88   | 2,200     |
| 11 | 50,80   | 2,000     |
| 10 | 45,72   | 1,800     |
| 9  | 40,64   | 1,600     |
| 8  | 35,56   | 1,400     |
| 7  | 30,48   | 1,200     |
| 6  | 25,40   | 1,000     |
| 5  | 20,32   | 0,800     |
| 4  | 15,24   | 0,600     |
| 3  | 10,16   | 0,400     |
| 2  | 5,08    | 0,200     |
| n  | L1 [mm] | L1 [Inch] |

For the mounting of PCBs, it should be noted that the rated data relates only to the PCB components alone.  
The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 664 / VDE 0110.  
The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application.  
Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

SHOWN: SLS 5.08/04/180F

|                  |                    |            |                              |          |                                                             |                   |  |
|------------------|--------------------|------------|------------------------------|----------|-------------------------------------------------------------|-------------------|--|
|                  | METRIC TOLERANCES: |            | 53611/5<br>06.10.10 HERTEL_S |          | 01                                                          | CAT.NO.: .        |  |
|                  | X.                 | = ±0.3     | MODIFICATION                 |          |                                                             | <b>Weidmüller</b> |  |
|                  | DRAWN              | 26.03.2007 | NAME                         | HERTEL_S | <b>SLS 5.08/.. /180 F(FI)..</b><br>STIFTLISTE<br>PIN HEADER |                   |  |
|                  | RESPONSIBLE        |            | NAME                         | HERTEL_S |                                                             |                   |  |
| SCALE: 2:1       | CHECKED            | 06.10.2010 | HECKERT_M                    |          |                                                             |                   |  |
| SUPERSEDES: .    | APPROVED           |            | HECKERT_M                    |          | PRODUCT FILE: SLS 5.08                                      |                   |  |
| SUPERSEDED BY: . |                    |            |                              |          | 7314                                                        |                   |  |

**C 34205** **03**  
DRAWING NO. SHEET 01 OF 02 SHEETS  
ISSUE NO.