

We reserve the right to make technical changes

Technical drawing of a mechanical component, showing multiple views and dimensions:

- Top View:** Shows overall dimensions: 15.90 (width), 11.90 (inner width), 8.66 (height), 6.81 (inner height), 11.43 (inner width), and 15.70 (outer width). A detail 'C' is indicated.
- Front View:** Shows dimensions: 21.35±0.20 (width), 13.8 (height), 13.5 (inner height), 1.30 (width), 3.05 (width), 10.75 (width), 2.54±0.2 (height), 8.89±0.2 (width), and 3.30±0.51 (height). A 'tin' label points to a feature.
- Bottom View:** Shows dimensions: 1.27 (width), 1.27x7=8.89 (width), and 1.27 (width).
- Detail 'C':** A magnified view of the detail 'C' from the top view, showing dimensions: 3.30 (width), Ø3.10 (hole diameter), 2.55 (height), 2.30 (height), 3.82 (height), R0.60 (radius), and 1.10 (width).
- Bottom View (Detailed):** Shows dimensions: 8.89 (width), 2.54 (height), 1.27x7=8.89 (width), 8 (number of holes), 8-Ø0.90 (hole pattern), 2-Ø1.70 (hole pattern), 2-Ø3.20 (hole pattern), 11.43 (width), 15.70 (width), 3.05 (height), and 1.27 (width).

PCB Layout
Component Side Shown