



PS 2.0
Order NO. 031000 0000



GENERAL TOLERANCE:
DIN ISO 2768-m

P = Pitch
n = No. of Poles
l = Pin length
Shown: LX15.00/04/90/...

10	135,00	5,315
9	120,00	4,724
8	105,00	4,134
7	90,00	3,543
6	75,00	2,953
5	60,00	2,362
4	45,00	1,772
3	30,00	1,181
2	15,00	0,591
n	L1 [mm]	L1 [inch]

6,5	0/-0,35
4,5	0/-0,35
3	30,00
2	15,00
n	L1 [mm]

6,5	0/-0,35
4,5	0/-0,35
3	30,00
2	15,00
n	L1 [mm]

6,5	0/-0,35
4,5	0/-0,35
3	30,00
2	15,00
n	L1 [mm]

 EC00000683	00	Prim PLM Part No.: 009292	Prim ERP Part No.: 1226480000	29942		
				Max. nos.	Modification	Issue no.
				14.05.2018		29
					Date	Sheet 01 of 04 sheets
					Name	
					Drawn	03.12.2018 Xiang, Keqin
					Responsible	Xiang, Keqin
				Scale: 1/1	Approved	04.12.2018 Xu, Shary
				Size: A3		
				Drawings Assembly		Product file: 7234 LX 15.00

For the mounting of PCBs, it should be noted that the rated data relates only to the PCB components alone. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 60664-1 (VDE 0110). The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 60326-3 very fine.

Weidmüller PCB components are tested to the IEC 60947-7-4 standard, and are valid for its field of application. Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.