




⑩



4-9 POLE



10-20 POLE

**KUNDENZEICHNUNG**  
**CUSTOMER DRAWING**

20	72.39	2.850
19	68.58	2.700
18	64.77	2.550
17	60.96	2.400
16	57.15	2.250
15	53.34	2.100
14	49.53	1.950
13	45.72	1.800
12	41.91	1.650
11	38.10	1.500
10	34.29	1.350
9	30.48	1.200
8	26.67	1.050
7	22.86	0.900
6	19.05	0.750
5	15.24	0.600
4	11.43	0.450
3		
2		
N	L1 [mm]	L1 [inch]

Cat. no.:

C 40383 10

Drawing no.:

Sheet 05 of 06 sheets

Issue no.:

<b>GENERAL TOLERANCE:</b> <b>DIN ISO 2768-m</b>			
98178/5 16.10.17 MA_J		01	
Modification			
 <b>Max. nos.</b>			
		Date	Name
Drawn	21.02.2006	GU_D	
Responsible		MA_J	
Scale: 2/1	Checked	16.10.2017	ZHOU_N
Supersedes: .	Approved		XU_S
Product file: BCZ 3.81			

**Weidmüller** 

**BCZ 3.81/.../180LRZE SN ...**  
BUCHSENLEISTE  
SOCKET BLOCK

7070

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.