


M 1/1




12	83,82	3,30
11	76,20	3,00
10	68,58	2,70
9	60,96	2,40
8	53,34	2,10
7	45,72	1,80
6	38,10	1,50
5	30,48	1,20
4	22,86	0,90
3	15,24	0,60
2	7,62	0,30
n	L1 (mm)	L1 (inch)

DARGESTELLT/ SHOWN: SLF7.62HP/04/180

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

GENERAL TOLERANCE: DIN ISO 2768-mK		Cat. no.:	
94118/5 23.04.18 HELIS_MA		00	
Modification			
	Date	Name	
	Drawn	12.04.2018 HELIS_MA	
	Responsible	DOMRATH_M	
	Scale: 2:1	Checked	24.04.2018 HELIS_MA
	Supersedes: .	Approved	NOLTE_S
		Product file: BLF/SLF7.62HP	
		Drawing no. 3 46068 Issue no. 03 Sheet 01 of 04 sheets	
 SLF 7.62HP/..180 STIFTLEISTE PIN HEADER			