






SHOWN: BVZ 7.62HP/04/180FC...



SHOWN: BVZ 7.62HP/04/180SFC...


 ALLGEMEINGEÜLTIGE KUNDENZEICHNUNG, AKTUELLER STAND NUR AUF ANFRAGE
 GENERAL CUSTOMER DRAWING, TOPICAL VERSION ONLY IF REQUIRED

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

 GENERAL TOLERANCE:
 DIN ISO 2768-mK

 100963/5
 11.01.18 HELIS_MA 01

Modification

	Date	Name	Cat. no.:		
			Drawn	09.01.2007	NEUMANN_G
	Responsible				KRUG_M
Scale: 2:1	Checked	02.02.2018	HELIS_MA		
Supersedes: .	Approved		LANG_T	Product file: SV/BVZ 7.62	
				Drawing no. 3 42182 03	
				Issue no. Sheet 01 of 01 sheets	

Weidmüller

3 42182 03

Drawing no. Sheet 01 of 01 sheets

 BVZ 7.62HP/...FC
 BUCHSENLEISTE
 SOCKET CONNECTOR