

8000126354 PV combiner box thermal report**PV 112SXFXCXXV1O1TXPX15PWW****INPUT DATA**


Enclosure model	530 x 430 x 200 mm
Number of MPPT	6
Switch-disconnector model (per MPPT)	no switch-disconnector
Maximum current (per MPPT)	36 A
Number of inputs (per MPPT)	2
Fuse-link model	no fuse
Number of monitoring devices (per MPPT)	0
Type of mounting	Against wall, all other sides detached
Maximum allowed internal temperature	70 °C
Combined inputs	1
Height (A)	530 mm
Width (B)	430 mm
Depth (C)	200 mm
Effective cooling surface A_e of the enclosure	0.63 m ²

RESULTS

Ambient temperature (no direct sunlight)	35 °C
Rated current per input at 35°C	18.00 A
Power dissipated by components (except wiring)	0 W
Power dissipated by wiring	4 W
Total dissipated power	4 W
Temperature rise, mid height	3 °C
Temperature rise, top	3 °C
Internal temperature, top	38 °C

CURRENT RATINGS

At 35°C	18.00 A
At 40°C	18.00 A
At 45°C	18.00 A
At 50°C	18.00 A

**NOTES**

Thermal report based on IEC TR 60890 ed2.0

Thermal report does not include the direct sunlight effects