



Ref. Certif. No.

JPTUV-102220-M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

Weidmüller Interface GmbH & Co. KG
Klingenbergstr. 26
32758 Detmold, Germany

Name and address of the manufacturer

Weidmüller Interface GmbH & Co. KG
Klingenbergstr. 26
32758 Detmold, Germany

Name and address of the factory

See additional page(s)

Ratings and principal characteristics

Input : 100-240VAC, 50/60Hz, 4-2A; Class I
Output: 1) 24VDC, 10A; 2) 48VDC, 5A

Trademark (if any)

Weidmüller

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

- 1) PRO MAX 240W 24V 10A
- 2) PRO MAX 240W 48V 5A

Additional information (if necessary may also be reported on page 2)

For model differences, refer to the test report.
Re-issue of JPTUV-102220 dated 10.12.2019,
due to first modification.

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014
See Test Report for National Differences

As shown in the Test Report Ref. No. which forms part of this Certificate

50308353 002

This CB Test Certificate is issued by the National Certification Body



TÜV Rheinland Japan Ltd.
Global Technology Assessment Center
4-25-2 Kita-Yamata, Tsuzuki-ku
Yokohama 224-0021, Japan
Phone + 81 45 914-3888
Fax + 81 45 914-3354
Mail: info@jpn.tuv.com
Web : www.tuv.com

Date: 2023-06-12

Signature:

Sommy Chen

10061 CB 06/20/09 IK