











General customer drawing, topical version only if required

⑩

Screwdriver and conductor direction



For the mounting of PCBs, it should be noted that the rated data relates only to the PCB components alone. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 60664-1 (VDE 0110). The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 60326-3 very fine.

Weidmüller PCB components are tested to the IEC 60947-7-4 standard, and are valid for its field of application. Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.



General Tolerances: WN700144-W.. WN 212010 ISO 2768-mK

Changes: EC00005454 1

Mat. No. (SAP) 2473020000

Drawings Assembly

Drawn Xiang, Keqin

Responsible Xiang, Keqin

Approved Xu, Shary

18.01.2022

12	82.50	3.248
11	75.00	2.953
10	67.50	2.657
9	60.00	2.362
8	52.50	2.067
7	45.00	1.772
6	37.50	1.476
5	30.00	1.181
4	22.50	0.886
3	15.00	0.591
2	7.50	0.295
n	L1 [mm]	L1 [inch]
Poles		

P = 0.295° (Pitch)
D = 0.079°
d = 1.5×0.8
 $0.059^{\circ} \times 0.031^{\circ}$
l = $5.0 \pm 0.2 - 0.6$
 0.197°

61340

10

Drawing no. Index

Scale: 2:1 Sheet 2 / 4

Weidmüller

LLFS 7.50/.../90 ...
PCB TERMINAL
LEITERPLATTENKLEMME

A3