




WEITERGABE SOWIE VERVIELFÄLTIGUNG DIESES DOKUMENTS, VERWERTUNG UND MITTEILUNG SEINES INHALTS SIND VERBOTEN, SOWEIT NICHT AUSDRUECKLICH GESTATTET.  
ZUWIDERHANDLUNGEN VERPFLICHTEN ZU SCHADENERSATZ. ALLE RECHTE FUER DEN FALL DER PATENT-, GEBRAUCHSMUSTER- ODER GESCHMACKSMUSTEREINTRAGUNG VORBEHALTEN.  
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.  
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. WEIDMUELLER EXCLUSIVELY RESERVES THE RIGHT TO FILE FOR PATENTS, UTILITY MODELS OR DESIGNS.

© WEIDMUELLER INTERFACE GmbH & Co.KG

MASSE OHNE TOLERANZ SIND KEINE PRUEFMASSE  
DIMS. WITHOUT TOLERANCE ARE NOT CONTROL DIMS.

DIE DEUTSCHE VERSION IST VERBINDLICH  
THE GERMAN VERSION IS BINDING



|    |         |           |
|----|---------|-----------|
| 12 | 82,50   | 3,248     |
| 11 | 75,00   | 2,953     |
| 10 | 67,50   | 2,657     |
| 9  | 60,00   | 2,362     |
| 8  | 52,50   | 2,067     |
| 7  | 45,00   | 1,772     |
| 6  | 37,50   | 1,476     |
| 5  | 30,00   | 1,181     |
| 4  | 22,50   | 0,886     |
| 3  | 15,00   | 0,591     |
| 2  | 7,50    | 0,295     |
| n  | L1 [mm] | L1 [Inch] |

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller PCB components are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

|                      |                                                               |                                                      |                                 |                           |                                         |  |
|----------------------|---------------------------------------------------------------|------------------------------------------------------|---------------------------------|---------------------------|-----------------------------------------|--|
|                      | METRIC TOLERANCES:<br>X. = ±0.3<br>X.X = ±0.1<br>X.XX = ±0.05 |                                                      | 60233/5<br>09.11.11 HELIS_MA 01 |                           | CAT.NO.: .                              |  |
|                      | MODIFICATION                                                  |                                                      |                                 |                           | DRAWING NO. <b>C 21326</b> OF 02 SHEETS |  |
|                      |                                                               | DRAWN 16.08.2010                                     | DATE 16.08.2010                 | NAME HOHLBEIN_K           | ISSUE NO. <b>08</b>                     |  |
| RESPONSIBLE          |                                                               | CHECKED 11.11.2011                                   | NAME LANG_T                     | PRODUCT FILE: BLZ/SL 7.50 |                                         |  |
| SCALE: 2:1           |                                                               | APPROVED                                             | NAME HECKERT_M                  | 7152                      |                                         |  |
| SUPERSEDES: 21326/06 |                                                               | BLZ 7.50/././180...<br>BUCHSENLEISTE<br>SOCKET BLOCK |                                 |                           |                                         |  |