

8000096027 PV combiner box thermal report

PV 220S0F3CXXV1O0TXPX15LWW

INPUT DATA


Enclosure model	636 x 847 x 300 mm
Number of MPPT	1
Switch-disconnector model (per MPPT)	400A 1500V
Maximum current (per MPPT)	288 A
Number of inputs (per MPPT)	16
Fuse-link model	30A gPV 1500V 10x85mm
Number of monitoring devices (per MPPT)	0
Type of mounting	Against wall, all other sides detached
Maximum allowed internal temperature	70 °C
Combined inputs	1
Height (A)	636 mm
Width (B)	847 mm
Depth (C)	300 mm
Effective cooling surface A_e of the enclosure	1,45 m ²

RESULTS

Ambient temperature (no direct sunlight)	35 °C
Rated current per input at 35°C	24,66 A
Power dissipated by components (except wiring)	163 W
Power dissipated by wiring	23 W
Total dissipated power	187 W
Temperature rise, mid height	28 °C
Temperature rise, top	35 °C
Internal temperature, top	70 °C

CURRENT RATINGS

At 35°C	18,00 A
At 40°C	18,00 A
At 45°C	18,00 A
At 50°C	16,10 A



NOTES

Thermal report based on IEC TR 60890 ed2.0

Thermal report does not include the direct sunlight effects